

限用物質含有情況標示

Declaration of the Presence Condition of the Restricted Substances Marking

證書號碼 / 受理編號：
Certificate No / Application No.

設備名稱：無熔線斷路器 Moulded Case Circuit Breaker 型號（型式）：如下 Equipment Name Type designation (Type)						
S204 4P 63AF 50/60Hz Icn=Ics, 6kA at 220/380V B6, B10, B13, B16, B20, B25, B32, B40, B50, B63, C0. 5, C1, 1. 6, C2, C3, C4, C6, C8, C10, C13, C16, C20, C25, C32, C40, C50, C63, D0. 5, D1, D1. 6, D2, D3, D4, D6, D8, D10, D13, D16, D20, D25, D32, D40, D50, D63						
單元 Unit	限用物質及其化學符號 Restricted substances and its chemical symbols					
	鉛 Lead (Pb)	汞 Mercury (Hg)	鎘 Cadmium (Cd)	六價鉻 Hexavalent chromium (Cr ⁺⁶)	多溴聯苯 Polybrominated biphenyls (PBB)	多溴二苯醚 Polybrominated diphenyl ethers (PBDE)
外殼 (Housing)	○	○	○	○	○	○
切換機構 (Switching mechanism)	○	○	○	○	○	○
電磁跳脫裝置 (Magnetic release)	超出 0.1 wt %	○	○	○	○	○
積熱跳脫裝置 (Thermal release)	○	○	○	○	○	○
消弧系統 (Arc extinguishing system)	○	○	○	○	○	○
接線端子 (Terminals)	○	○	○	○	○	○
塑料部件 (Other plastic components)	○	○	○	○	○	○
備考1. “超出0.1 wt %”及“超出0.01 wt %”係指限用物質之百分比含量超出百分比含量基準值。 Note 1 : “Exceeding 0.1 wt %” and “exceeding 0.01 wt %” indicate that the percentage content of the restricted substance exceeds the reference percentage value of presence condition.						
備考2. “○”係指該項限用物質之百分比含量未超出百分比含量基準值。 Note 2 : “○” indicates that the percentage content of the restricted substance does not exceed the percentage of reference value of presence.						
備考3. “—”係指該項限用物質為排除項目。 Note 3 : The “—” indicates that the restricted substance corresponds to the exemption.						

系列型式：

S201 1P 63AF 50/60Hz Icn=Ics, 6kA at 220/380V

B6, B10, B13, B16, B20, B25, B32, B40, B50, B63, C0. 5, C1, 1. 6, C2, C3, C4, C6, C8, C10, C13, C16, C20, C25, C32, C40, C50, C63, D0. 5, D1, D1. 6, D2, D3, D4, D6, D8, D10, D13, D16, D20, D25, D32, D40, D50, D63

S201 1P+N 63AF 50/60Hz Icn=Ics, 6kA at 220/380V

B6, B10, B13, B16, B20, B25, B32, B40, B50, B63, C0. 5, C1, 1. 6, C2, C3, C4, C6, C8, C10, C13, C16, C20, C25, C32, C40, C50, C63, D0. 5, D1, D1. 6, D2, D3, D4, D6, D8, D10, D13, D16, D20, D25, D32, D40, D50, D63

S202 2P 63AF 50/60Hz Icn=Ics, 6kA at 220/380V

B6, B10, B13, B16, B20, B25, B32, B40, B50, B63, C0.5, C1, 1.6, C2, C3, C4, C6, C8, C10, C13, C16, C20, C25, C32, C40, C50, C63, D0.5, D1, D1.6, D2, D3, D4, D6, D8, D10, D13, D16, D20, D25, D32, D40, D50, D63

S203 3P 63AF 50/60Hz Icn=Ics, 6kA at 220/380V

B6, B10, B13, B16, B20, B25, B32, B40, B50, B63, C0.5, C1, 1.6, C2, C3, C4, C6, C8, C10, C13, C16, C20, C25, C32, C40, C50, C63, D0.5, D1, D1.6, D2, D3, D4, D6, D8, D10, D13, D16, D20, D25, D32, D40, D50, D63

S203 3P+N 63AF 50/60Hz Icn=Ics, 6kA at 220/380V

B6, B10, B13, B16, B20, B25, B32, B40, B50, B63, C0.5, C1, 1.6, C2, C3, C4, C6, C8, C10, C13, C16, C20, C25, C32, C40, C50, C63, D0.5, D1, D1.6, D2, D3, D4, D6, D8, D10, D13, D16, D20, D25, D32, D40, D50, D63