

# Metallic Systems

## LFH-SPL Conduit



### Technical Characteristics

Conforms to	BSI Kitemark KM-35161 Low voltage directive NF F16-101 (I1 F1) London Underground 1-085
-------------	--

Approvals and Standards	   
-------------------------	--

Degree of mechanical protection	Medium flexibility & fatigue life
---------------------------------	-----------------------------------

Degree of protection	IP69k - with SPL type M fitting IP68 - with SPL type M fitting IP67 - with SPL type A, B & M fittings IP66 - with SPL type M & C90 fittings
----------------------	--


UV protection	High
---------------	------

Finish	Black
--------	-------

Application	Rail, Buildings - where low smoke & toxicity is a primary concern
-------------	---

Normal operating temperature range	Application	Min Temp	Max Temp
	Static	- 20°C	+90°C
	Dynamic	- 5°C	+105°C

For use with - Fitting range	<a href="#">Adaptasteel</a> - Type <a href="#">A</a> , <a href="#">B</a> , <a href="#">E</a> , <a href="#">M</a> <a href="#">C90</a> & <a href="#">45</a>
------------------------------	---

Fire performance	Test Standard	Performance Rating	(See Fire testing <a href="#">data</a> for fire performance overview)
	EN 45545	HL3	
	NFF16-101	I1 F1	
	LUL-1085	✓	
	BS 6853	Class 1a	
	DIN 5510-2	N/A	

Testing data	Click or See pages <a href="#">3</a> & <a href="#">4</a>
--------------	--

Type of material	Galvanised steel core, string packing up to 32mm, interlocked core 40mm and above - Low Fire Hazard jacket
------------------	--



# Metallic Systems


## LFH-SPL Conduit



### Technical & Dimensional Data

Conduit size metric (mm)	10	12	16	20	25	32	40	50	63
Conduit size US trade (inches)	1/4"	5/16"	3/8"	1/2"	3/4"	1"	1 1/4"	1 1/2"	2"
Part code	-	-	LFH-SPL	LFH-SPL	LFH-SPL	LFH-SPL	LFH-SPL	LFH-SPL	LFH-SPL
Coil length (m)	-	-	10/25	10/25	10/25	10/25	10	10	10
A - Outside diameter (mm)	-	-	17.0	21.5	26.0	34.0	44.5	55.0	64.5
B - Inside diameter (mm)	-	-	13.0	16.9	21.4	28.1	37.7	48.4	57.5
C - Static bend radius (mm)	-	-	35	45	55	60	80	90	115
Average weight (KG/100m)	-	-	23.0	31.2	37	58.2	94.9	115.6	76.8

*For ordering code add coil length to part code - e.g LFH-SPL25/25M*



# Metallic Systems

## LFH-SPL Conduit



### BS EN 61386 Classification

	Fitting	Compression	Impact	Min temp	Max temp	bending	electrical	IP solids	IP water	Corrosion	Tensile	Non-flame Propogating	Suspended load
LFH-SPL	SPL(M)	4	4	2	3	4	2	6	7	-	4	1	5

### Mechanical Properties

Test Type	Methods / Standards	Requirements	Value
Crush Strength @ 23°C	IEC61386-1	<25% crush >90% recovery	>1250N
Crush Strength @ 23 °C	-	10% Crush, Instantaneous Value	1800N
Impact Strength @ 23 °C	IEC61386-1	No Cracks <20% deformation	>20J
Impact Strength @-5 °C	IEC61386-1	No Cracks. <20% deformation	>6J
Tensile Strength	IEC61386-1	With M Type Fitting	>1000N
Tensile Strength	-	Ultimate pull-out of M-Type Fitting	1600N
Dynamic Bend radius @ -5 °C	IEC61386-23	5000 cycles minimum	4xOD

### Thermal Properties

Test Type	Methods / Standards	Requirements	Value
Minimum Temperature	IEC61386-23	Dynamic 5000 cycles	-5°C
Maximum Temperature	IEC61386-23	Dynamic 5000 cycles	105°C
Minimum Static		Permanent Use	-20°C
Maximum Static		Permanent Use	90°C

### Chemical Resistance Chart

**Key:**

Suitable : ●

Limited Suitability : ●

Unsuitable : ●

Not Tested : ●

<span style="color: red;">●</span> Astm No.1	<span style="color: yellow;">●</span> Diesel oil	<span style="color: red;">●</span> Methyl Bromide	<span style="color: yellow;">●</span> Sulphur Dioxide (Gas)
<span style="color: yellow;">●</span> Astm No.2	<span style="color: green;">●</span> Diethylamine	<span style="color: red;">●</span> MEK	<span style="color: green;">●</span> Sulphuric Acid (10%)
<span style="color: yellow;">●</span> Astm No.3	<span style="color: yellow;">●</span> Ethanol	<span style="color: green;">●</span> Nitric Acid (10%)	<span style="color: yellow;">●</span> Sulphuric Acid (70%)
<span style="color: green;">●</span> Acetic Acid (10%)	<span style="color: red;">●</span> Ether	<span style="color: red;">●</span> Nitric Acid (70%)	<span style="color: yellow;">●</span> Toluene
<span style="color: red;">●</span> Acetone	<span style="color: yellow;">●</span> Ethylamine	<span style="color: green;">●</span> Oxalic Acid	<span style="color: yellow;">●</span> Transformer Oil
<span style="color: green;">●</span> Aluminium Chloride	<span style="color: green;">●</span> Ethylene Glycol	<span style="color: green;">●</span> Ozone (Gas)	<span style="color: yellow;">●</span> 1,1,1-Trichloroethane
<span style="color: yellow;">●</span> Aniline	<span style="color: red;">●</span> Ethyl Ethanoate	<span style="color: yellow;">●</span> Paraffin oil	<span style="color: yellow;">●</span> Trichloroethylene
<span style="color: red;">●</span> Benzaldehyde	<span style="color: red;">●</span> Freon 32	<span style="color: red;">●</span> Petrol	<span style="color: red;">●</span> Turpentine
<span style="color: red;">●</span> Benzene	<span style="color: red;">●</span> Hydrochloric Acid (10%)	<span style="color: red;">●</span> Phenol	<span style="color: yellow;">●</span> Vegetable Oil
<span style="color: red;">●</span> Carbon tetrachloride	<span style="color: red;">●</span> Hydrochloric Acid (36%)	<span style="color: green;">●</span> Sea Water	<span style="color: red;">●</span> Vinyl Acetate
<span style="color: yellow;">●</span> Chlorine water	<span style="color: yellow;">●</span> Hydrogen Peroxide (35%)	<span style="color: green;">●</span> Silver Nitrate	<span style="color: green;">●</span> Water
<span style="color: red;">●</span> Chloroform	<span style="color: red;">●</span> Hydrogen Peroxide (87%)	<span style="color: red;">●</span> Skydrol	<span style="color: yellow;">●</span> White Spirit
<span style="color: green;">●</span> Citric Acid	<span style="color: green;">●</span> Lactic Acid	<span style="color: green;">●</span> Sodium Chloride	<span style="color: green;">●</span> Zinc Chloride
<span style="color: green;">●</span> Copper Sulphate	<span style="color: yellow;">●</span> Lubricating oil	<span style="color: green;">●</span> Sodium Hydroxide (10%)	
<span style="color: red;">●</span> Cresol	<span style="color: yellow;">●</span> Methanol	<span style="color: green;">●</span> Sodium Hydroxide (60%)	

The information above is given as a guide only and is based on published technical data and experience. The chemical resistance of the above products is dependant on factors such as chemical exposure, concentration of the chemical and temperature. The above chemicals are valid for a temperature of 23°C. Use of the above table is at the users own discretion and risk. Those using it must satisfy themselves that their application presents no health and safety risks. The end user should assess compatibility with their application and contact Thomas & Betts for further information.

ADHERENCE TO THE CURRENT WIRING REGULATIONS BS7671 OR NEC WIRING REGULATIONS (FOR USA) IS STRONGLY ADVISED.

MINIMUM BEND RADIUS FOR FLEXING IS DEPENDANT UPON MINIMUM TEMPERATURE, BENDING FREQUENCY AND CHEMICAL ENVIRONMENT.

**Cable Management Products Ltd.**

CMG House - Station Road - Coleshill - B46 1HT - United Kingdom

Tel: +44(0)1675 468 222 - Fax: +44(0)1675 464 930

Technical Support e-mail: [cmg.conduitsystems@tnb.com](mailto:cmg.conduitsystems@tnb.com) - [www.adaptaflex.com](http://www.adaptaflex.com)



A Member of the ABB Group

The Company's policy is one of continuous improvement and reserves the right to change specifications at any time without prior notice.

# Metallic Systems

## LFH-SPL Conduit



### Flammability

Test Type	Method / Standard	Requirement	Result	Unit
Oxygen Index	ISO 4589-2	% Oxygen to support combustion	51.9	%
Glow Wire Rating	IEC 60695	No Ignition to Extinguish with 30s	960	°C
Flammability	UL94	Vertical (V0, V2) or Horizontal (HB)	V0	
Flammability	IEC 61386-1	1Kw Burner @ 45°	Pass	Pass/Fail

### Smoke

Test Type	Method / Standard	Requirement	Result	Unit
Smoke Density	NF X 10-702	Vos <sub>4</sub>	34.7	Pass
Smoke Density	NF X 10.702	D Max	290	Pass
Smoke Density	BS6853	A <sub>0</sub> < 0.02	0.006	A <sub>0</sub>
Smoke Density	ISO - 5659-2	D <sub>s</sub> Max < 100	46	None

### Toxicity

Test Type	Method / Standard	Requirement	Result	Unit
Halogen Free	LUL	< 0.5%	Yes	Yes/No
Phosphorous Free	LUL	< 0.5%	Yes	Yes/No
Sulphur Free	LUL	< 0.5%	Yes	Yes/No
Toxicity	NFX70 - 100 1 / 2	CIT <sub>NLP</sub>	0.07	None
Toxicity	BS 6853 D8.3	R	0.34	None

### Fire Performance Overview

Property	Low Fire Hazard	Enhanced Low Fire Hazard	Super Low Fire Hazard	Inherent Low Fire Hazard
<b>Property</b>	<b>LFH</b>	<b>EFLH</b>	<b>SLFH</b>	<b>ILFH</b>
Oxygen Index ISO4589	32% ≥ OI ≥ 28%	OI ≥ 32%	OI ≥ 32%	Inherent Low Fire Hazard i.e
BS6853 Smoke Density 3m <sup>3</sup>	0.02 ≤ A <sub>0</sub> ≤ 0.03	0.0005 ± A <sub>0</sub> ≤ 0.02	A <sub>0</sub> ≤ 0.005	Type , S, SS
Zero Halogen	✓	✓	✓	Metallic Conduit & Fittings
Zero Phosphorus	✓	✓	✓	
Zero Sulphur	✓	✓	✓	
NFF16-102	I3F2	I2F2	I2F1	
EN45545-2	HL2	HL3	HL3	

### Pre Test Conditions

Duration	Standard	Temperature	Relative Humidity
168 (Hours)	IEC61386	23 (°C)	50 (%)

Cable Management Products Ltd.

CMG House - Station Road - Coleshill - B46 1HT - United Kingdom

Tel: +44(0)1675 468 222 - Fax: +44(0)1675 464 930

Technical Support e-mail: [cmg.conduitsystems@tnb.com](mailto:cmg.conduitsystems@tnb.com) - [www.adaptaflex.com](http://www.adaptaflex.com)

**Thomas & Betts**

A Member of the ABB Group

The Company's policy is one of continuous improvement and reserves the right to change specifications at any time without prior notice.