

Non-Metallic Systems

Adaptalok Type C90



Technical Characteristics

Conforms to BSI Kitemark KM-35161
 Low voltage directive
 Lloyd's Register of Shipping (Type Approval)
 NFF 16-10/12 I4,F2
 UL1696 Recognition (Metric and NPT Threads - Indoor dry locations only)

Approvals and Standards



Degree of mechanical protection High Impact Resistance

Degree of protection

IP66 - As standard
 IP67 - When fitted with ALS Seal
 IP68 - When fitted with ALS Seal (1.1 Bar 35 mins)
 IP69k - When fitted with ALS Seal

ALS Seal



UV protection

Very High

Fitting Characteristics

90° Elbow - Fixed external male thread
 Black (BL) as standard or Grey (GR) - RAL 7031

Application

For insertion into threaded entries or knockouts using a locknut to secure (Locknuts Supplied with METRIC Threads Only)

Normal operating temperature range

Application	Min Temp	Max Temp
Static	- 50°C	+120°C
Dynamic	- 45°C	+120 °C

For use with - Conduit Series

Light, Standard and Heavyweight variants of [PA](#), [PI](#), [CP](#), [PR](#), [PADL](#) & [PF](#)

Fire performance

Test Standard	Performance Rating	
BS EN 61386-1 & 23	Approved	
NFF16-101	I4 F2	Self Extinguishing Low Smoke & Halogen Free
ISO 4589-2	24%	
BS EN 60695-2-11	850°C	
UL94	V2	

Testing data

Click or See pages [6](#) & [7](#)

Type of material

Polyamide (Nylon) 66 - Body

Image



Non-Metallic Systems


Adaptalok Type C90



Dimensional & Thread Data

Part No BlackBody Metric Threads	Part No Grey Body Metric Threads	Thread A	Nominal Dimensions (mm)						Weight in grams (Each)
			B	C	D	E	F	G	
AL10/M12/C90/BL	AL10/M12/C90/BL	M12 x 1.5	8.0	17.8	16.1	15.3	41.1	6.1	4
AL13/M16/C90/BL	AL13/M16/C90/BL	M16 x 1.5	11.5	31.5	21.2	22.0	52.9	11.3	8
AL16/M16/C90/BL	AL16/M16/C90/BL	M16 x 1.5	11.5	33.1	23.9	22.0	54.7	11.3	10
AL16/M20/C90/BL	AL16/M20/C90/BL	M20 x 1.5	13.0	33.1	23.9	27.0	54.7	15.2	12
AL21/M20/C90/BL	AL21/M20/C90/BL	M20 x 1.5	13.0	36.1	29.2	27.0	56.5	15.2	14
AL28/M25/C90/BL	AL28/M25/C90/BL	M25 x 1.5	15.0	45.1	37.0	32.1	64.5	20.2	23
AL34/M32/C90/BL	AL34/M32/C90/BL	M32 x 1.5	16.0	57.0	43.4	38.9	73.7	25.9	40
AL42/M40/C90/BL	AL42/M40/C90/BL	M40 x 1.5	16.0	73.5	54.5	47.5	92.2	34.0	70
AL54/M50/C90/BL	AL54/M50/C90/BL	M50 x 1.5	16.0	95.1	67.9	59.0	115.0	40.2	120
AL54/M63/C90/BL	AL54/M63/C90/BL	M63 x 1.5	16.0	95.1	67.9	70.0	115.0	50.0	120

Metric	Standard thread conforming to EN60423 & BS3643		
	Thread Size	Ext Thread Outside Diameter	Int Thread Inside Diameter
M12	12mm	10.9mm	1.5mm
M16	16mm	14.4mm	1.5mm
M20	20mm	18.4mm	1.5mm
M25	25mm	23.4mm	1.5mm
M32	32mm	30.4mm	1.5mm
M40	40mm	38.4mm	1.5mm
M50	50mm	48.4mm	1.5mm
M63	63mm	61.4mm	1.5mm



NOTE: Dimensions are nominal

Non-Metallic Systems


Adaptalok Type C90



Dimensional & Thread Data

Part No Black Body PG Threads	Part No Grey Body PG Threads	Thread A	Nominal Dimensions (mm)						Weight in grams (Each)
			B	C	D	E	F	G	
AL10/PG7/C90/BL	AL10/PG7/C90/GR	PG7	8.0	17.8	16.1	15.3	41.1	6.1	4
AL13/PG9/C90/BL	AL13/PG9/C90/GR	PG9	10.0	31.7	21.2	22.0	52.9	11.2	8
AL16/PG9/C90/BL	AL16/PG9/C90/GR	PG9	10.0	33.2	23.89	22.0	54.7	11.2	9
AL16/PG11/C90/BL	AL16/PG11/C90/GR	PG11	10.0	33.2	23.9	25.0	54.7	14.4	11
AL16/PG13/C90/BL	AL16/PG13/C90/GR	PG13.5	10.0	33.2	23.9	26.7	54.7	14.7	11
AL21/PG13/C90/BL	AL21/PG13/C90/GR	PG13.5	10.0	36.1	29.2	27.1	56.5	14.7	13
AL21/PG16/C90/BL	AL21/PG16/C90/GR	PG16	11.5	36.1	29.2	27.1	56.5	15.2	14
AL28/PG21/C90/BL	AL28/PG21/C90/GR	PG21	12.2	45.0	37.0	35.5	64.0	21.9	23
AL34/PG29/C90/BL	AL34/PG29/C90/GR	PG29	12.2	57.0	43.4	44.0	74.2	29.0	41
AL42/PG36/C90/BL	AL42/PG36/C90/GR	PG36	12.0	73.5	54.5	53.7	92.2	39.1	72
AL54/PG48/C90/BL	AL54/PG48/C90/GR	PG48	12.0	95.1	67.9	67.6	115.0	50.8	135

PG	German Standard Thread Conforming to DIN40430		
Thread Size	Ext Thread Outside Diameter	Int Thread Inside Diameter	Pitch
PG7	12.5mm	11.3mm	1.27mm
PG9	15.2mm	13.9mm	1.41mm
PG11	18.6mm	17.3mm	1.41mm
PG13.5	20.4mm	19.1mm	1.41mm
PG16	22.5mm	21.2mm	1.41mm
PG21	28.3mm	26.8mm	1.59mm
PG29	37mm	35.5mm	1.59mm
PG36	47mm	45.5mm	1.59mm
PG48	59.3mm	57.8mm	1.59mm



NOTE: Dimensions are nominal

Non-Metallic Systems

Adaptalok Type C90




Dimensional & Thread Data

Part No Black Body NPT Threads	Part No Grey Body NPT Threads	Thread A	Nominal Dimensions (mm)						Weight in grams (Each)
			B	C	D	E	F	G	
AL13/038/C90/GR	AL13/038/C90/GR	3/8"	11.5	31.8	21.2	22.0	52.9	11.3	8
AL16/038/C90/GR	AL16/038/C90/GR	3/8"	11.5	33.3	23.9	22.0	54.7	11.3	10
AL16/050/C90/GR	AL16/050/C90/GR	1/2"	13.0	33.3	23.9	27.0	54.7	15.2	12
AL21/050/C90/GR	AL21/050/C90/GR	1/2"	13.0	36.1	29.2	27.0	56.5	15.2	14
AL28/075/C90/GR	AL28/075/C90/GR	3/4"	15.0	45.1	37.0	33.0	64.5	20.2	24
AL34/100/C90/GR	AL34/100/C90/GR	1"	16.0	57.0	43.4	40.0	73.7	25.9	40
AL42/125/C90/GR	AL42/125/C90/GR	1 1/4"	16.0	73.5	54.5	48.5	92.2	34.0	43
AL54/150/C90/GR	AL54/150/C90/GR	1 1/2"	16.0	95.1	67.9	59.0	115.0	40.2	118
AL54/200/C90/GR	AL54/200/C90/GR	2"	16.0	95.1	67.9	65.5	115.0	50.0	128

NPT	US taper seal pipe thread conforming to ANSI/ASME B1.20.1-1983	
Thread Size	Ext Thread Outside Diameter	Pitch
3/8"	16.7mm	1.14mm
1/2"	21.0mm	1.81mm
3/4"	26.4mm	1.81mm
1"	33.3mm	2.21mm
1 1/4"	41.9mm	2.21mm
1 1/2"	47.8mm	2.21mm
2"	59.6mm	2.21mm

NOTE: Dimensions are nominal



Non-Metallic Systems

Adaptalok Type C90




Dimensional & Thread Data

Part No Black Body PF Threads	Part No Grey Body PF Threads	Thread A	Nominal Dimensions (mm)						Weight in grams (Each)
			B	C	D	E	F	G	
AL13/PF038/C90/GR	AL13/PF038/C90/GR	3/8"	11.5	31.8	21.2	22.0	52.9	11.3	8.3
AL16/PF038/C90/GR	AL16/PF038/C90/GR	3/8"	11.5	33.3	23.9	22.0	54.7	11.3	9.7
AL16/PF050/C90/GR	AL16/PF050/C90/GR	1/2"	13.0	33.3	23.9	27.0	54.7	15.2	11.1
AL21/PF050/C90/GR	AL21/PF050/C90/GR	1/2"	13.0	36.1	29.2	27.0	56.5	15.2	13.3
AL28/PF075/C90/GR	AL28/PF075/C90/GR	3/4"	15.0	45.1	37.0	33.0	64.5	20.2	24.5
AL34/PF100/C90/GR	AL34/PF100/C90/GR	1"	16.0	57.0	43.4	40.0	73.7	25.9	41.0
AL42/PF125/C90/GR	AL42/PF125/C90/GR	1 1/4"	16.0	73.5	54.5	48.5	92.2	34.0	68.8
AL54/PF150/C90/GR	AL54/PF150/C90/GR	1 1/2"	16.0	95.1	67.9	59.0	115.0	40.2	120.0
AL54/PF00/C90/GR	AL54/PF00/C90/GR	2"	16.0	95.1	67.9	65.5	115.0	59.8	125.0

PF	Japanese Standard thread conforming to JIS B 0202		
Thread Size	Ext Thread Outside Diameter	Int Thread Inside Diameter	Pitch
3/8"	16.7mm	15.0mm	1.34mm
1/2"	21.0mm	18.6mm	18.1mm
3/4"	26.4mm	24.1mm	1.81mm
1"	33.3mm	30.3mm	2.31mm
1 1/4"	41.9mm	39.0mm	2.31mm
1 1/2"	47.8mm	44.8mm	2.31mm
2"	59.6mm	56.7mm	2.31mm

NOTE: Dimensions are nominal



Non-Metallic Systems

Adaptalok Type C90



BS EN 61386 Classification

	Fitting	Compression	Impact	Min temp	Max temp	bending	electrical	IP solids	IP water	Corrosion	Tensile	Non-flame Propogating	Suspended load
	AL	N/A	4	2	4	N/A	0	6	6	0	1	1	0

Mechanical Properties

Test Type	Methods / Standards	Requirements	Value
Tensile Strength	IEC61386-1	2 mins at Specified Value (<i>PAFS21 Conduit</i>)	Class 1
Tensile Strength		Ultimate Pullout (<i>PAFS21 Conduit</i>)	240N
Impact Strength @ -45°C	IEC61386-1	No visible damage	Class 1
Impact Strength @ -5°C	IEC61386-1	No visible damage	Class 3
Impact Strength @ 23°C	IEC61386-1	No visible damage	Class 5

Tensile Tests to IEC 61386 gives the minimum classification value only. Actual values will depend on the type and size of the fittings used and will always be greater than the minimum – Impact strength is the minimum classification value at the minimum temperature – actual values will depend on size and temperature. Specific values available on request.

Thermal Properties

Test Type	Methods / Standards	Requirements	Value
Dynamic Applications	IEC 61386-23	5000 Operations at MBR 2hrs	-45°C to +120°C
Static Short Term Temp		Temporary Use (3000hrs)	-50°C to +120°C
Static Long Term Temp		Permanent Use (30,000) Hours	-40°C to +105°C

Non-Metallic Systems

Adaptalok Type C90



Flammability

Test Type	Method / Standard	Requirement	Result	Unit
Glow Wire	BS EN 60695-2-11	Extinguish within 30s	850°C	°C
Flammability	IEC 61386-1-12	1Kw Burner Flame to Self Extinguish	Pass	Pass/Fail
Oxygen Index	ISO 4589-2		24.1	%
Ignition Rating	NF F16-101	I Rating	I4	-

Smoke

Test Type	Method / Standard	Requirement	Result	Unit
Fume Rating	NF F16-101	F Rating	F2	-

Toxicity

Test Type	Method / Standard	Requirement	Result	Unit
Halogen Free	NFX 70-100	< 0.5%	Pass	Pass/Fail

Pre Test Conditions

Duration	Standard	Temperature	Relative Humidity
168 (Hours)	IEC61386	23 (°C)	50 (%)

Chemical Resistance Chart

Key:	●	●	●	●
Suitable :	●	●	●	●
Limited Suitability :	●	●	●	●
Unsuitable :	●	●	●	●
Not Tested :	●	●	●	●

● Astm No.1	● Diesel oil	● Methyl Bromide	● Sulphur Dioxide (Gas)
● Astm No.2	● Diethylamine	● MEK	● Sulphuric Acid (10%)
● Astm No.3	● Ethanol	● Nitric Acid (10%)	● Sulphuric Acid (70%)
● Acetic Acid (10%)	● Ether	● Nitric Acid (70%)	● Toluene
● Acetone	● Ethylamine	● Oxalic Acid	● Transformer Oil
● Aluminium Chloride	● Ethylene Glycol	● Ozone (Gas)	● 1,1,1-Trichloroethane
● Aniline	● Ethyl Ethanoate	● Paraffin oil	● Trichloroethylene
● Benzaldehyde	● Freon 32	● Petrol	● Turpentine
● Benzene	● Hydrochloric Acid (10%)	● Phenol	● Vegetable Oil
● Carbon tetrachloride	● Hydrochloric Acid (36%)	● Sea Water	● Vinyl Acetate
● Chlorine water	● Hydrogen Peroxide (35%)	● Silver Nitrate	● Water
● Chloroform	● Hydrogen Peroxide (87%)	● Skydrol	● White Spirit
● Citric Acid	● Lactic Acid	● Sodium Chloride	● Zinc Chloride
● Copper Sulphate	● Lubricating oil	● Sodium Hydroxide (10%)	
● Cresol	● Methanol	● Sodium Hydroxide (60%)	

The information above is given as a guide only and is based on published technical data and experience. The chemical resistance of the above products is dependant on factors such as chemical exposure, concentration of the chemical and temperature. The above chemicals are valid for a temperature of 23°C. Use of the above table is at the users own discretion and risk. Those using it must satisfy themselves that their application presents no health and safety risks. The end user should assess compatibility with their application and contact Thomas & Betts for further information.

ADHERENCE TO THE CURRENT WIRING REGULATIONS BS7671 OR NEC WIRING REGULATIONS (FOR USA) IS STRONGLY ADVISED.
 MINIMUM BEND RADIUS FOR FLEXING IS DEPENDANT UPON MINIMUM TEMPERATURE, BENDING FREQUENCY AND CHEMICAL ENVIRONMENT.