

Non-Metallic Systems

Adaptalok Type PPA



Technical Characteristics

Conforms to Low voltage directive

Approvals and Standards



Degree of mechanical protection High Impact Resistance

Degree of protection IP66 - As standard

UV protection Medium

Fitting Characteristics



Straight fitting - Fixed external male thread
Black (BL) Only

Application

For insertion into threaded entries or knockouts using a locknut to secure
(Locknuts Supplied with METRIC Threads Only)

Normal operating temperature range

Application	Min Temp	Max Temp
Static	- 20°C	+90°C
Dynamic	- 5°C	+105 °C

For use with - Conduit Series

Medium weight polypropylene [PP](#)

Fire performance

Test Standard

Performance Rating

Not Rated

Not Rated

Testing data

Click or See pages [3](#) & [4](#)

Type of material

Polypropylene

Image



The Company's policy is one of continuous improvement and reserves the right to change specifications at any time without prior notice.

Non-Metallic Systems


Adaptalok Type PPA



Dimensional & Thread Data

Part No Black Body Metric Threads	Thread A	Nominal Dimensions (mm)						Weight in grams (Each)
		B	C	D	E	F	G	
AL13/M16/PPA/BL	M16x1.5	11.5	33.0	21.3	11.6	19.0	17.0	5
AL16/M16/PPA/BL	M16x1.5	11.5	33.0	23.7	11.6	23.7	19.8	6
AL21/M20/PPA/BL	M20x1.5	14.0	34.7	28.9	14.8	26.7	25.0	9
AL28/M25/PPA/BL	M25x1.5	16.2	36.8	36.8	20.0	35.5	32.3	14
AL34/M32/PPA/BL	M32x1.5	16.0	37.8	43.2	26.5	41.5	38.9	20

Metric	Standard thread conforming to EN60423 & BS3643		
Thread Size	Ext Thread Outside Diameter	Int Thread Inside Diameter	Pitch
M12	12mm	10.9mm	1.5mm
M16	16mm	14.4mm	1.5mm
M20	20mm	18.4mm	1.5mm
M25	25mm	23.4mm	1.5mm
M32	32mm	30.4mm	1.5mm
M40	40mm	38.4mm	1.5mm
M50	50mm	48.4mm	1.5mm
M63	63mm	61.4mm	1.5mm



NOTE: Dimensions are nominal

The Company's policy is one of continuous improvement and reserves the right to change specifications at any time without prior notice.

Non-Metallic Systems

Adaptalok Type PPA



BS EN 61386 Classification

Fitting	Compression	Impact	Min temp	Max temp	bending	electrical	IP solids	IP water	Corrosion	Tensile	Non-flame Propogating	Suspended load
AL	N/A	4	2	4	N/A	0	6	6	0	1	1	0

Mechanical Properties

Test Type	Methods / Standards	Requirements	Value
Tensile Strength	IEC61386-1	2 mins at Specified Value (<i>PPFMS21 Conduit</i>)	Class 1
Tensile Strength		Ultimate Pullout (<i>PPFMS21 Conduit</i>)	200N
Impact Strength @ -5°C	IEC61386-1	No visible damage	Class 2
Impact Strength @ 23°C	IEC61386-1	No visible damage	Class 4

Tensile Tests to IEC 61386 gives the minimum classification value only. Actual values will depend on the type and size of the fittings used and will always be greater than the minimum – Impact strength is the minimum classification value at the minimum temperature – actual values will depend on size and temperature. Specific values available on request.

Thermal Properties

Test Type	Methods / Standards	Requirements	Value
Dynamic Applications	IEC 61386-23	5000 Operations at MBR 2hrs	-5°C to +105°C
Static Short Term Temp		Temporary Use (3000hrs)	-20°C to +105°C
Static Long Term Temp		Permanent Use (30,000) Hours	-20°C to +90°C

Chemical Resistance Chart

Key:

Suitable :



Limited Suitability :



Unsuitable :



Not Tested :



Astm No.1	Diesel oil	Methyl Bromide	Sulphur Dioxide (Gas)
Astm No.2	Diethylamine	MEK	Sulphuric Acid (10%)
Astm No.3	Ethanol	Nitric Acid (10%)	Sulphuric Acid (70%)
Acetic Acid (10%)	Ether	Nitric Acid (70%)	Toluene
Acetone	Ethylamine	Oxalic Acid	Transformer Oil
Aluminium Chloride	Ethylene Glycol	Ozone (Gas)	1,1,1-Trichloroethane
Aniline	Ethyl Ethanoate	Paraffin oil	Trichloroethylene
Benzaldehyde	Freon 32	Petrol	Turpentine
Benzene	Hydrochloric Acid (10%)	Phenol	Vegetable Oil
Carbon tetrachloride	Hydrochloric Acid (36%)	Sea Water	Vinyl Acetate
Chlorine water	Hydrogen Peroxide (35%)	Silver Nitrate	Water
Chloroform	Hydrogen Peroxide (87%)	Skydrol	White Spirit
Citric Acid	Lactic Acid	Sodium Chloride	Zinc Chloride
Copper Sulphate	Lubricating oil	Sodium Hydroxide (10%)	
Cresol	Methanol	Sodium Hydroxide (60%)	

The information above is given as a guide only and is based on published technical data and experience. The chemical resistance of the above products is dependant on factors such as chemical exposure, concentration of the chemical and temperature. The above chemicals are valid for a temperature of 23°C. Use of the above table is at the users own discretion and risk. Those using it must satisfy themselves that their application presents no health and safety risks. The end user should assess compatibility with their application and contact Thomas & Betts for further information.

ADHERENCE TO THE CURRENT WIRING REGULATIONS BS7671 OR NEC WIRING REGULATIONS (FOR USA) IS STRONGLY ADVISED.

MINIMUM BEND RADIUS FOR FLEXING IS DEPENDANT UPON MINIMUM TEMPERATURE, BENDING FREQUENCY AND CHEMICAL ENVIRONMENT.

The Company's policy is one of continuous improvement and reserves the right to change specifications at any time without prior notice.

Cable Management Products Ltd.

CMG House - Station Road - Coleshill - B46 1HT - United Kingdom
 Tel: +44(0)1675 468 222 - Fax: +44(0)1675 464 930

Technical Support e-mail: cmg.conduitsystems@tnb.com - www.adaptaflex.co.uk



A Member of the ABB Group