


# EXB Range - Anti-static conduit Ex e Non Metallic System



## Features

- Electrostatically discharging
- Very good UV-Resistance
- For indoor and outdoor applications
- Very high mechanical load capacity and low temperature impact strength
- High abrasion resistance
- Free from halogens and cadmium
- For use with EXPQ Fittings

## Approvals



## Certification & Standards

<b>Approved to:</b>	EN/IEC 60079-0, 60079-7, 60079-31
<b>EC TYPE Examination Certificate:</b>	Baseefa 08 ATEX 0003X IECEx BAS08.0001X Ex e IIC Gb Ex tb IIIC Db
<b>Temperature range:</b>	-20°C to +80°C Sizes 03-08 -40°C to +85°C Sizes 09-10
<b>Special Characteristics:</b>	Surface resistivity <106 Ω

Compatible with: EXPQM / EXPQA fittings / Materials: Anti-Static Nylon 12 / Colour: ● Black

Multilayer Conduit	Conduit Size (mm)		Outside Diameter (mm)	Bend Radius (mm)		Coil Lengths (m)	GID Code's
	Metric	NW		Static	Dynamic		
EXB0350	16	12	15.8	30	70	50	7TCA297120R0008
EXB0450	21	17	21.2	40	75	50	7TCA297120R0011
EXB0550	28	23	28.5	45	90	50	7TCA297120R0014
EXB0650	34	29	34.4	55	110	50	7TCA297120R0017
EXB0730	42	36	42.4	60	160	30	7TCA297120R0019
EXB0830	54	48	54.5	70	200	30	7TCA297120R0022
EXB0910	63	56	67.2	110	250	10	7TCA297120R0420
EXB1010	80	70	80	150	330	10	7TCA297120R0420

CMG House, Station Road, Coleshill, Birmingham, B46 1HT United Kingdom

Tel: +44 (0) 1675 468 213 | Email: sales@kopex.co.uk

[www.tnb-hazardous.com](http://www.tnb-hazardous.com)

The Company's policy is one of continuous improvement and reserves the right to change specifications at any time without prior notice.

Power and productivity  
for a better world™

