



| ID | Description | Date | By | Appr. |
|----|-------------|------|----|-------|
|    |             |      |    |       |
|    |             |      |    |       |
|    |             |      |    |       |

| Tolerance  | >0,5 =3<br>±0,1 | > =6<br>±0,1 | >6 =30<br>±0,2 | >30 =120<br>±0,3 | >120 =400<br>±0,5 | >400 =1000<br>±0,8 |
|------------|-----------------|--------------|----------------|------------------|-------------------|--------------------|
| ISO 2768-m |                 |              |                |                  |                   |                    |

|   |          |   |                   |            |
|---|----------|---|-------------------|------------|
| 2   | PMR107.2 | Asennusrengas   | 1                 | - g        |
| 1   | PMR106   | -   | 1                 | 0.0        |
| Part  | Code     | Description   | Pcs               | Weight [g] |
| Material:   |          | Mat. Code:  |                   |            |
| Supplier:   |          | Tool No:  | Weight [g] 5974.8 | Volume:    |
|  |          |  | Replaces:         |            |
|   |          |   | SAP Code:         |            |
| Scale   |          | Date  | Drw No:           |            |
| 3:2   |          | By  | Ref:              |            |
| A3  |          | Checked   | Code:             |            |
| Sheet No: 1 (1)   |          | Ctrl  |                   |            |