

AF116-30-11-11



AF116-30-11-11 Contactor

General Information

Extended Product Type	AF116-30-11-11
Product ID	1SFL427001R1111
EAN	7320500476352
Catalog Description	AF116-30-11-11 Contactor
Long Description	A 3-phase Contactor suitable for various applications such as Motor starting, Isolation, By-pass and Distribution application up to max 690 V. Operated with wide control voltage range 24-60 V, 50 and 60 Hz, 20-60 V DC

Classifications

Object Classification Code	Q
ETIM 4	EC000066 - Magnet contactor, AC-switching
ETIM 5	EC000066 - Magnet contactor, AC-switching
ETIM 6	EC000066 - Power contactor, AC switching
ETIM 7	EC000066 - Power contactor, AC switching
UNSPSC	39121529
IDEA Granular Category Code (IGCC)	4755 >> Contactors
E-Number (Norway)	4117611
E-Number (Sweden)	3210066

Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	194 mm
Package Level 1 Depth / Length	115 mm
Package Level 1 Height	169 mm
Package Level 1 Gross Weight	1.75 kg
Package Level 1 EAN	7320500476352

Certificates and Declarations (Document Number)

ABS Certificate	14-LD1092198-PDA
BV Certificate	BV_36353_A0BV
CB Certificate	SEMKO_SE-70479M1
CCC Certificate	2013010304604055
CCS Certificate	GB14T00030

cUL Certificate	20120925-E36588
Declaration of Conformity - CE	2CMT2015-005439
DNV Certificate	DNV_E-14043
DNV GL Certificate	DNV_E-14043
EAC Certificate	9AKK107046A8618
Environmental Information	2CMT004732
GL Certificate	DNV_E-14043
Instructions and Manuals	1SFC100003M0201
LR Certificate	LR_14_70011(E1)
PRS Certificate	TE_2092_880423_16
RINA Certificate	ELE060313XG_002
RMRS Certificate	9AKK107045A6978
RoHS Information	2CMT2015-005439
UL Listing Card	UL_E36588

Technical UL/CSA

Maximum Operating Voltage UL/CSA	Main Circuit 600 V
General Use Rating UL/CSA	(600 V AC) 160 A
Horsepower Rating UL/CSA	(208 V AC) Three Phase 30 Hp (440 ... 480 V AC) Three Phase 75 Hp (550 ... 600 V AC) Three Phase 100 Hp (220 ... 240 V AC) Three Phase 40 Hp (200 V AC) Three Phase 30 Hp

Environmental

Ambient Air Temperature	Close to Contactor Fitted with Thermal O/L Relay (0.85 ... 1.1 Uc) -25 ... +50 °C Close to Contactor without Thermal O/L Relay (0.85 ... 1.1 Uc) -40 ... +70 °C Close to Contactor for Storage -40 ... +70 °C
Maximum Operating Altitude Permissible	3000 m
RoHS Status	Following EU Directive 2011/65/EU

Technical

Number of Main Contacts NO	3
Number of Main Contacts NC	0
Number of Auxiliary Contacts NO	1
Number of Auxiliary Contacts NC	1
Rated Operational Voltage	Main Circuit 690 V
Rated Frequency (f)	Main Circuit 50/60 Hz
Conventional Free-air Thermal Current (I_{th})	acc. to IEC 60947-4-1, Open Contactors q = 40 °C 160 A
Rated Operational Current AC-1 (I_e)	(690 V) 55 °C 145 A (690 V) 40 °C 160 A (690 V) 70 °C 130 A
Rated Operational Current AC-3 (I_e)	(220 / 230 / 240 V) 55 °C 116 A (690 V) 55 °C 65 A (415 V) 55 °C 116 A (440 V) 55 °C 116 A (380 / 400 V) 55 °C 116 A (500 V) 55 °C 110 A
Rated Operational Power AC-3 (P_e)	(220 / 230 / 240 V) 30 kW (380 / 400 V) 55 kW (415 V) 55 kW

	(440 V) 75 kW (500 V) 75 kW (690 V) 55 kW
Rated Breaking Capacity AC-3 acc. to IEC 60947-4-1	8 x I _e AC-3
Rated Making Capacity AC-3 acc. to IEC 60947-4-1	10 x I _e AC-3
Short-Circuit Protective Devices	gG Type Fuses 250 A
Rated Short-time Withstand Current (I _{cw})	at 40 °C Ambient Temp, in Free Air, from a Cold State 10 s 928 A at 40 °C Ambient Temp, in Free Air, from a Cold State 15 min 160 A at 40 °C Ambient Temp, in Free Air, from a Cold State 30 s 536 A at 40 °C Ambient Temp, in Free Air, from a Cold State 1 s 1160 A at 40 °C Ambient Temp, in Free Air, from a Cold State 1 min 379 A
Maximum Breaking Capacity	cos phi=0.45 (cos phi=0.35 for I _e > 100 A) at 440 V 2000 A cos phi=0.45 (cos phi=0.35 for I _e > 100 A) at 690 V 1000 A
Maximum Electrical Switching Frequency	AC-3 300 cycles per hour AC-1 300 cycles per hour AC-2 / AC-4 150 cycles per hour
Rated Operational Current DC-1 (I _e)	(110 V) 2 Poles in Series, 40 °C 145 A (220 V) 3 Poles in Series, 40 °C 145 A
Rated Operational Current DC-3 (I _e)	(110 V) 2 Poles in Series, 40 °C 145 A (220 V) 3 Poles in Series, 40 °C 145 A
Rated Operational Current DC-5 (I _e)	(110 V) 2 Poles in Series, 40 °C 145 A (220 V) 3 Poles in Series, 40 °C 145 A
Rated Insulation Voltage (U _i)	acc. to UL/CSA 600 V acc. to IEC 60947-4-1 and VDE 0110 (Gr. C) 690 V
Rated Impulse Withstand Voltage (U _{imp})	Main Circuit 8 kV
Mechanical Durability	5 million
Maximum Mechanical Switching Frequency	300 cycles per hour
Coil Operating Limits	(acc. to IEC 60947-4-1) 0.85 x U _c Min. ... 1.1 x U _c Max. (at θ ≤ 70 °C) °C
Rated Control Circuit Voltage (U _c)	60 Hz 24 ... 60 V 50 Hz 24 ... 60 V DC Operation 20 ... 60 V
Coil Consumption	Pull-in at Max. Rated Control Circuit Voltage 60 Hz 225 V·A Holding at Max. Rated Control Circuit Voltage DC 2.5 W Holding at Max. Rated Control Circuit Voltage 50 Hz 5.5 V·A Pull-in at Max. Rated Control Circuit Voltage DC 210 W Pull-in at Max. Rated Control Circuit Voltage 50 Hz 225 V·A Holding at Max. Rated Control Circuit Voltage 60 Hz 5.5 V·A
Operate Time	Between Coil De-energization and NO Contact Opening 37 ... 47 ms Between Coil Energization and NO Contact Closing 25 ... 55 ms
Connecting Capacity Main Circuit	Flexible 1 x 10 ... 70 mm ² Rigid Cu-Cable 1 x 10 ... 95 mm ²
Connecting Capacity Auxiliary Circuit	Solid 1 x 1 ... 4 mm ² Flexible with Insulated Ferrule 2 x 0.75 ... 2.5 mm ² Stranded 2 x 1 ... 4 mm ² Flexible 2x0.75 ... 2.5 mm ² Flexible with Ferrule 2 x 0.75 ... 2.5 mm ²
Degree of Protection	acc. to IEC 60529, IEC 60947-1, EN 60529 Coil Terminals IP20 acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP00
Terminal Type	Double Clamp

Dimensions

Product Net Width	90 mm
Product Net Depth / Length	126 mm
Product Net Height	150 mm
Product Net Weight	1.644 kg

Popular Downloads

Data Sheet, Technical Information	1SBC100192C0206
Instructions and Manuals	1SFC100003M0201
Dimension Diagram	1SFB535001G1051

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85364900

Categories

Low Voltage Products and Systems → Control Products → Contactors → Block Contactors

