

AF205-30-11-11



AF205-30-11-11 Contactor

General Information

Extended Product Type	AF205-30-11-11
Product ID	1SFL527002R1111
EAN	7320500480540
Catalog Description	AF205-30-11-11 Contactor
Long Description	A 3-phase Contactor suitable for various applications such as Motor starting, Isolation, By-pass and Distribution application up to max 1000 V. Operated with wide control voltage range 24-60 V, 50 and 60 Hz, 20-60 V DC

Classifications

Object Classification Code	Q
ETIM 4	EC000066 - Magnet contactor, AC-switching
ETIM 5	EC000066 - Magnet contactor, AC-switching
ETIM 6	EC000066 - Power contactor, AC switching
ETIM 7	EC000066 - Power contactor, AC switching
UNSPSC	39121529
IDEA Granular Category Code (IGCC)	4755 >> Contactors
E-Number (Norway)	4117642
E-Number (Sweden)	3210140

Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	200 mm
Package Level 1 Depth / Length	220 mm
Package Level 1 Height	280 mm
Package Level 1 Gross Weight	3 kg
Package Level 1 EAN	7320500480540

Certificates and Declarations (Document Number)

ABS Certificate	14-LD1092198-PDA
BV Certificate	BV_36353_A0BV
CB Certificate	SE-82315
CCC Certificate	CQC_2014010304676685
CCS Certificate	GB14T00030

cUL Certificate	20121023-E36588
Declaration of Conformity - CE	2CMT2015-005439
DNV Certificate	DNV_E-14043
DNV GL Certificate	DNV_E-14043
EAC Certificate	9AKK107046A8618
Environmental Information	2CMT004732
GL Certificate	GL_95072-14HH
Instructions and Manuals	1SFC100008M0201
KC Certificate	9AKK107046A9912
LR Certificate	LR_14_70011(E1)
PRS Certificate	TE_2092_880423_16
RINA Certificate	ELE060313XG_002
RMRS Certificate	9AKK107045A6978
RoHS Information	2CMT2015-005439
UL Listing Card	UL_E36588

Technical UL/CSA

Maximum Operating Voltage UL/CSA	Main Circuit 600 V
General Use Rating UL/CSA	(600 V AC) 300 A
Horsepower Rating UL/CSA	(208 V AC) Three Phase 60 Hp (440 ... 480 V AC) Three Phase 150 Hp (550 ... 600 V AC) Three Phase 200 Hp (220 ... 240 V AC) Three Phase 75 Hp (200 V AC) Three Phase 60 Hp

Environmental

Ambient Air Temperature	Close to Contactor Fitted with Thermal O/L Relay (0.85 ... 1.1 Uc) -25 ... +50 °C Close to Contactor without Thermal O/L Relay (0.85 ... 1.1 Uc) -40 ... +70 °C Close to Contactor for Storage -40 ... +70 °C
Maximum Operating Altitude Permissible	3000 m
RoHS Status	Following EU Directive 2011/65/EU

Technical

Number of Main Contacts NO	3
Number of Main Contacts NC	0
Number of Auxiliary Contacts NO	1
Number of Auxiliary Contacts NC	1
Rated Operational Voltage	Main Circuit 1000 V
Rated Frequency (f)	Main Circuit 50/60 Hz
Conventional Free-air Thermal Current (I_{th})	acc. to IEC 60947-4-1, Open Contactors q = 40 °C 350 A
Rated Operational Current AC-1 (I_e)	(690 V) 55 °C 300 A (690 V) 40 °C 350 A (1000 V) 40 °C 275 A (1000 V) 55 °C 250 A (690 V) 70 °C 240 A (1000 V) 70 °C 200 A
Rated Operational Current AC-3 (I_e)	(1000 V) 55 °C 100 A (690 V) 55 °C 165 A (415 V) 55 °C 205 A (220 / 230 / 240 V) 55 °C 205 A (440 V) 55 °C 205 A

	(380 / 400 V) 55 °C 205 A (500 V) 55 °C 165 A
Rated Operational Power AC-3 (P_e)	(220 / 230 / 240 V) 55 kW (380 / 400 V) 110 kW (415 V) 110 kW (440 V) 132 kW (500 V) 110 kW (690 V) 160 kW (1000 V) 132 kW
Rated Breaking Capacity AC-3 acc. to IEC 60947-4-1	8 x I_e AC-3
Rated Making Capacity AC-3 acc. to IEC 60947-4-1	10 x I_e AC-3
Short-Circuit Protective Devices	gG Type Fuses 400 A
Rated Short-time Withstand Current (I_{cw})	at 40 °C Ambient Temp, in Free Air, from a Cold State 10 s 1640 A at 40 °C Ambient Temp, in Free Air, from a Cold State 30 s 947 A at 40 °C Ambient Temp, in Free Air, from a Cold State 15 min 350 A at 40 °C Ambient Temp, in Free Air, from a Cold State 1 s 2050 A at 40 °C Ambient Temp, in Free Air, from a Cold State 1 min 670 A
Maximum Breaking Capacity	cos phi=0.45 (cos phi=0.35 for $I_e > 100$ A) at 440 V 3500 A cos phi=0.45 (cos phi=0.35 for $I_e > 100$ A) at 690 V 2500 A
Maximum Electrical Switching Frequency	AC-3 300 cycles per hour AC-1 300 cycles per hour AC-2 / AC-4 150 cycles per hour
Rated Operational Current DC-1 (I_e)	(110 V) 2 Poles in Series, 40 °C 275 A (220 V) 3 Poles in Series, 40 °C 275 A
Rated Operational Current DC-3 (I_e)	(110 V) 2 Poles in Series, 40 °C 275 A (220 V) 3 Poles in Series, 40 °C 275 A
Rated Operational Current DC-5 (I_e)	(110 V) 2 Poles in Series, 40 °C 275 A (220 V) 3 Poles in Series, 40 °C 275 A
Rated Insulation Voltage (U_i)	acc. to UL/CSA 600 V acc. to IEC 60947-4-1 and VDE 0110 (Gr. C) 1000 V
Rated Impulse Withstand Voltage (U_{imp})	Main Circuit 8 kV
Mechanical Durability	5 million
Maximum Mechanical Switching Frequency	300 cycles per hour
Coil Operating Limits	(acc. to IEC 60947-4-1) 0.85 x U_c Min. ... 1.1 x U_c Max. (at $\theta \leq 70$ °C) °C
Rated Control Circuit Voltage (U_c)	60 Hz 24 ... 60 V 50 Hz 24 ... 60 V DC Operation 20 ... 60 V
Coil Consumption	Pull-in at Max. Rated Control Circuit Voltage 60 Hz 165 V·A Holding at Max. Rated Control Circuit Voltage DC 2.5 W Holding at Max. Rated Control Circuit Voltage 50 Hz 6 V·A Pull-in at Max. Rated Control Circuit Voltage DC 205 W Pull-in at Max. Rated Control Circuit Voltage 50 Hz 165 V·A Holding at Max. Rated Control Circuit Voltage 60 Hz 6 V·A
Operate Time	Between Coil De-energization and NO Contact Opening 37 ... 47 ms Between Coil Energization and NO Contact Closing 25 ... 55 ms
Connecting Capacity Main Circuit	Rigid Al-Cable 1 x 95 ... 185 mm ² Flexible 2 x 50 ... 95 mm ² Rigid Cu-Cable 2 x 50 ... 120 mm ²
Connecting Capacity Auxiliary Circuit	Solid 2 x 1 ... 4 mm ² Flexible with Insulated Ferrule 2 x 0.75 ... 2.5 mm ² Stranded 2 x 1 ... 4 mm ² Flexible 2x0.75 ... 2.5 mm ² Flexible with Ferrule 1 x 0.75 ... 2.5 mm ²
Degree of Protection	acc. to IEC 60529, IEC 60947-1, EN 60529 Coil Terminals IP20 acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP00
Terminal Type	Main Circuit: Bars

Dimensions

Product Net Width	105 mm
-------------------	--------

Product Net Depth / Length	152 mm
Product Net Height	196 mm
Product Net Weight	2.778 kg

Popular Downloads

Data Sheet, Technical Information	1SBC100192C0206
Instructions and Manuals	1SFC100008M0201
Dimension Diagram	1SFB535001G1056

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85364900

Categories

Low Voltage Products and Systems → Control Products → Contactors → Block Contactors

