

PRODUCT-DETAILS

ACS550-01-195A-4+C135

ACS550-01-195A-4+C135,205A,380V,IP21,for flange mounting, not including mounting set



General Information	
Global Commercial Alias	ACS550-01-195A-4+C135
Product ID	3ABD00027110
ABB Type Designation	ACS550-01-195A-4+C135
Catalog Description	ACS550-01-195A-4+C135,205A,380V,IP21,for flange mounting, not including mounting set
Long Description	ACS550-01-195A-4+C135,205A,380V,IP21,for flange mounting, not including mounting set

Ordering	
Country of Origin	China (CN)
Customs Tariff Number	85044099
Invoice Description	ACS550-01-195A-4+C135,205A,380V,IP21,for flange mounting, not including mounting set
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions	
Product Net Weight	45 kg
Product Net Depth / Length	814 mm
Product Net Height	306 mm
Product Net Width	315 mm
Package Level 1 Depth / Length	970 mm
Package Level 1 Height	560 mm
Package Level 1 Width	370 mm
Package Level 1 Units	0 carton

Technical	
Number of Phases	3
Degree of Protection	IP21
Enclosure Type NEMA	Type1
Frequency (f)	47.5 ... 63 Hz
Frame Size	R6
Input Voltage (U_{in})	380 ... 500 V
Mounting Type	Wall-mounted_NO UNIT\$
Output Current, Heavy-Duty Use (I_{HD})	162 A
Output Current, Normal Use (I_n)	205 A
Output Power, Heavy-Duty Use (P_{HD})	90 kW
Output Power, Normal Use (P_n)	110 kW
Efficiency Level	IE2
Complete Drive Module Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Relative Loss	Efficiency
0 / 25 %	615 W	0.4 %	92.6 %
0 / 50 %	910 W	0.6 %	94.2 %
0 / 100 %	1661 W	1.2 %	94.6 %
50 / 25 %	689 W	0.5 %	95.9 %
50 / 50 %	1061 W	0.7 %	96.7 %
50 / 100 %	1990 W	1.4 %	96.8 %
90 / 50 %	1279 W	0.9 %	97.8 %
90 / 100 %	2497 W	1.8 %	97.8 %

Additional Information	
Product Name	Frequency Converter

Classifications	
-----------------	--

UNSPSC

39122001

Environmental

WEEE Category

4. Large Equipment (Any External Dimension More Than 50 cm)

Categories

Drives → Low Voltage AC Drives → Legacy AC Drives → ACS550-01 - Wall-mounted drive

