

OT800E03P



OT800E03P SWITCH-DISCONNECTOR



General Information

Extended Product Type	OT800E03P
Product ID	1SCA022718R9410
EAN	6417019230528
Catalog Description	OT800E03P SWITCH-DISCONNECTOR
Long Description	3-pole, front operated, base mounted switch-diconnector with black IP65 handle and shaft, terminal bolt kit included

Popular Downloads

Data Sheet, Technical Information	1SCC301020C0201
Instructions and Manuals	1SCC301042M0211
Mechanical Drawings	1SCC301330F0001 1SCC301329F0001 OT600_800E03.igs

Dimensions

Product Net Width	266 mm
Product Net Height	250 mm
Product Net Depth / Length	140 mm
Product Net Weight	6.4 kg

Technical

Rated Operational Current AC-21A (I_e)	(380 ... 415 V) 800 A (500 V) 800 A (690 V) 800 A (1000 V) 800 A
Rated Operational Current AC-22A (I_e)	(380 ... 415 V) 800 A (500 V) 800 A (690 V) 800 A
Rated Operational Current AC-23A (I_e)	(380 ... 415 V) 800 A (500 V) 800 A (690 V) 800 A
Rated Operational Power AC-23A (P_e)	(220 ... 240 V) 250 kW (400 ... 415 V) 450 kW (500 V) 560 kW (690 V) 800 kW
Conventional Free-air Thermal Current (I_{th})	q = 40 °C 800 A
	Fully Enclosed 800 A

Conventional Thermal Current (I_{the})	
Rated Impulse Withstand Voltage (U_{imp})	12 kV
Rated Insulation Voltage (U_i)	acc. to IEC/EN 60664-1 1000 V
Rated Operational Voltage	Main Circuit 1000 V
Rated Short-Circuit Making Capacity (I_{cm})	(690 V) 80 kA
Rated Short-time Withstand Current (I_{cw})	for 1 s 20 kA
Power Loss	at Rated Operating Conditions per Pole 40 W
Pollution Degree	3
Handle Color	Black
Handle Type	Handle and shaft included
Switches Operating Mechanism	Mechanism at the End of the Switch 03 (Left Side)
Distance Between Phases	Standard
Position of Line Terminals	Top In - Bottom Out Bottom In - Top Out
Operating Mode	Front operated
Standards	IEC 60947-3
Special Functions	No
Mounting Type	Base mounting
Number of Poles	3
Degree of Protection	Front IP00
Terminal Type	Lug terminals
Terminal Width	39 mm
Tightening Torque	acc. IEC 60947-1 50...75 N·m
Mechanical Durability	10000

Environmental

RoHS Status	Following EU Directive 2011/65/EU
Environmental Information	1SCC301149D0202

Certificates and Declarations (Document Number)

BV Certificate	1SCC301103D0201
Declaration of Conformity - CE	1SCC301140D2704
DNV GL Certificate	1SCC301184D0203
Environmental Information	1SCC301149D0202
Instructions and Manuals	1SCC301042M0211
RoHS Information	1SCC301149D0203

Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	260 mm
Package Level 1 Depth / Length	335 mm
Package Level 1 Height	152 mm
Package Level 1 Gross Weight	6.5 kg
Package Level 1 EAN	6417019230528

Classifications

Object Classification Code	Q
ETIM 5	EC000216 - Switch disconnecter
ETIM 6	EC000216 - Switch disconnecter
ETIM 7	EC000216 - Switch disconnecter
UNSPSC	39122233
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
E-Number (Sweden)	3171226

Categories

Low Voltage Products and Systems → Switches → Switch Disconnectors

