

PRODUCT-DETAILS

ACS580-04-650A-4

LV AC general purpose drive module, IEC: Pn 355 kW, 650 A (ACS580-04-650A-4)



General Information

Global Commercial Alias	ACS580-04-650A-4
Product ID	3ABD00036863-D
ABB Type Designation	ACS580-04-650A-4
Catalog Description	LV AC general purpose drive module, IEC: Pn 355 kW, 650 A (ACS580-04-650A-4)
Long Description	<p>The ACS580-04 is plug-in ready to control your compressors, conveyors, pumps, extruders, centrifuges, mixers, fans, and many other variable and constant torque applications, in a variety of light industries, including food and beverage, plastic, textile, material handling, and agriculture. All essential features are built-in as standard, simplifying drive selection, and making additional hardware unnecessary. A versatile and straightforward settings menu and assistants enable fast setup, commissioning, use, and maintenance, while a rugged and robust design makes it a good fit for various environments. With the ACS580 drives, you can easily take full control of your processes to comprehensively manage your plant. The ACS580-04 drive module comes in an IP00 enclosure as standard for cabinet installation. In addition, an IP20 enclosure is available.</p>

Ordering

Country of Origin	China (CN)
Customs Tariff Number	85044099
Invoice Description	ACS580-04-650A-4 PN: 355kW, IN: 650A
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece

Quote Only	No
Selling Unit of Measure	piece

Container Information

Gross Volume	0 dm³
--------------	-------

Dimensions

Product Net Weight	161 kg
Product Net Depth / Length	529 mm
Product Net Height	1462 mm
Product Net Width	345 mm
Package Level 1 Depth / Length	1000 mm
Package Level 1 Height	500 mm
Package Level 1 Width	400 mm
Package Level 1 Units	0 carton

Technical

Number of Phases	3
Degree of Protection	IP00
Enclosure Type NEMA	Open Type
Frequency (f)	47.5 ... 63 Hz
Frame Size	R10
Input Voltage (U _{in})	380 ... 480 V
Mounting Type	Cabinet-built_NO UNIT\$
Output Current, Heavy-Duty Use (I _{HD})	477 A
Output Current, Light-Overload Use (I _{LD})	634 A
Output Current, Normal Use (I _n)	650 A
Output Power, Heavy-Duty Use (P _{HD})	250 kW
Output Power, Light-Overload Use (P _{LD})	355 kW
Output Power, Normal Use (P _n)	355 kW
Efficiency Level	IE2
Complete Drive Module Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Relative Loss	Efficiency
0 / 25 %	2143 W	0.4 %	93.1 %
0 / 50 %	3094 W	0.6 %	94.8 %
0 / 100 %	5693 W	1.1 %	95.2 %
50 / 25 %	2306 W	0.4 %	96.3 %
50 / 50 %	3445 W	0.6 %	97.2 %
50 / 100 %	6585 W	1.2 %	97.3 %
90 / 50 %	3956 W	0.7 %	98.2 %
90 / 100 %	8046 W	1.5 %	98.1 %

Additional Information

Product Name	Frequency Converter
--------------	---------------------

Classifications

UNSPSC	39122001
--------	----------

Environmental

WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)
---------------	---

Categories

Drives → Low Voltage AC Drives → General Purpose Drives → ACS580-04 - Drive module

