

T6S 800 PR221DS-I In=800 3p F F



T6S 800 PR221DS-I In=800 3p F F

General Information

Extended Product Type	T6S 800 PR221DS-I In=800 3p F F
Product ID	1SDA060279R1
EAN	8015644627416
Catalog Description	T6S 800 PR221DS-I In=800 3p F F
Long Description	C.BREAKER TMAX T6S 800 FIXED THREE-POLE WITH FRONT TERMINALS AND SOLID-STATE RELEASE IN AC PR221DS-I R 800

Ordering

EAN	8015644627416
Minimum Order Quantity	1 piece
Customs Tariff Number	85362090

Dimensions

Product Net Width	210 mm
Product Net Height	268 mm
Product Net Depth / Length	103.5 mm
Product Net Weight	9.5 kg

Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	305 mm
Package Level 1 Height	285 mm
Package Level 1 Depth / Length	370 mm
Package Level 1 Gross Weight	11 kg
Package Level 1 EAN	8015644627416

Additional Information

Electrical Durability	5000 cycle 60 cycles per hour
Mechanical Durability	20000 cycle 120 cycles per hour
Number of Poles	3

Power Loss	at Rated Operating Conditions per Pole 32 W
Product Main Type	SACE Tmax T
Product Name	Moulded Case Circuit Breaker
Product Type	CB
Rated Current (I_n)	Main Circuit 800 A
Rated Impulse Withstand Voltage (U_{imp})	8 kV
Rated Insulation Voltage (U_i)	1000 V
Rated Operational Voltage	690 V AC
Rated Service Short-Circuit Breaking Capacity (I_{cs})	(220 V AC) 85 kA (230 V AC) 85 kA (380 V AC) 50 kA (400 V AC) 50 kA (415 V AC) 50 kA (440 V AC) 45 kA (500 V AC) 35 kA (690 V AC) 16,5 kA
Rated Short-time Withstand Current (I_{cw})	for 1 s 10 kA
Rated Ultimate Short-Circuit Breaking Capacity (I_{cu})	(220 V AC) 85 kA (230 V AC) 85 kA (380 V AC) 50 kA (400 V AC) 50 kA (415 V AC) 50 kA (440 V AC) 45 kA (500 V AC) 35 kA (690 V AC) 22 kA (250 V DC) 2 Poles in Series 50 kA (500 V DC) 2 Poles in Series 35 kA (750 V DC) 3 Poles in Series 20 kA
Rated Uninterrupted Current (I_u)	800 A
Release Type	EL
Standards	IEC
Sub-type	T6
Suitable For	T6
Suitable for Product Class	Moulded Case Circuit Breakers
Terminal Connection Type	Fixed Circuit-Breakers Front
Test Voltage Max (U_{test})	3500 V
Version	F

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	1SDC210015D0201
Declaration of Conformity - CE	1SDL000165R0006
Environmental Information	1SDL000143R0
Instructions and Manuals	1SDH000511R0001

Classifications

ETIM 4	EC000228 - Power circuit-breaker for trafo/generator/installation prot.
ETIM 5	EC000228 - Power circuit-breaker for trafo/generator/installation prot.
ETIM 6	EC000228 - Power circuit-breaker for trafo/generator/installation prot.
ETIM 7	EC000228 - Power circuit-breaker for trafo/generator/installation protection
Object Classification Code	Q
UNSPSC	39121100

—
Categories

Low Voltage Products and Systems → Circuit Breakers → Moulded Case Circuit Breakers → Tmax T

