

# A1A 125 TMF 100-1000 3p F F



A1A 125 TMF 100-1000 3p F F

## General Information

Extended Product Type	A1A 125 TMF 100-1000 3p F F
Product ID	1SDA066520R1
EAN	8015644004323
Catalog Description	A1A 125 TMF 100-1000 3p F F
Long Description	C.BREAKER FORMULA A1A 125 FIXED THREE-POLE WITH FRONT TERMINALS AND THERMOMAGNETIC RELEASE TMF R 100-1000 A

## Ordering

EAN	8015644004323
Minimum Order Quantity	1 piece
Customs Tariff Number	85362090

## Dimensions

Product Net Width	76.2 mm
Product Net Height	130 mm
Product Net Depth / Length	60 mm
Product Net Weight	0,792 kg

## Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	136.5 mm
Package Level 1 Height	124 mm
Package Level 1 Depth / Length	110.5 mm
Package Level 1 Gross Weight	0.8 kg
Package Level 1 EAN	8015644004323

## Additional Information

Electrical Durability	1500 cycle
Mechanical Durability	Nr. Operations 8500 cycle
Number of Poles	3
Opening Time	CB with SOR 15 ms CB with UVR 15 ms

Power Loss	at Rated Operating Conditions per Pole 8 W
Product Main Type	SACE FORMULA
Product Name	Moulded Case Circuit Breaker
Product Type	CB
Rated Current ( $I_n$ )	Main Circuit 100 A
Rated Impulse Withstand Voltage ( $U_{imp}$ )	6 kV
Rated Insulation Voltage ( $U_i$ )	690 V
Rated Operational Voltage	550 V AC 250 V DC
Rated Service Short-Circuit Breaking Capacity ( $I_{cs}$ )	(240 V AC) 12.5 kA (380 V AC) 5 kA (415 V AC) 5 kA (440 V AC) 4 kA (480 V AC) 3.75 kA (500 V AC) 2.5 kA (250 V DC) 2 Poles in Series 2.5 kA
Rated Ultimate Short-Circuit Breaking Capacity ( $I_{cu}$ )	(240 V AC) 10 kA (380 V AC) 10 kA (415 V AC) 10 kA (440 V AC) 8 kA (480 V AC) 7.5 kA (500 V AC) 5 kA (250 V DC) 5 kA
Rated Uninterrupted Current ( $I_u$ )	125 A
Release Type	TM
Standards	IEC
Sub-type	A1
Terminal Connection Type	Front
Version	F

## Certificates and Declarations (Document Number)

Data Sheet, Technical Information	1SDC210032D0204
Declaration of Conformity - CE	9AKK106713A5519
Environmental Information	1SDL000183R0001
Instructions and Manuals	1SDH000717R0001

## Classifications

ETIM 4	EC000228 - Power circuit-breaker for trafo/generator/installation prot.
ETIM 5	EC000228 - Power circuit-breaker for trafo/generator/installation prot.
ETIM 6	EC000228 - Power circuit-breaker for trafo/generator/installation prot.
ETIM 7	EC000228 - Power circuit-breaker for trafo/generator/installation protection
Object Classification Code	Q
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

## Categories

Low Voltage Products and Systems → Circuit Breakers → Moulded Case Circuit Breakers → FORMULA

