

PRODUCT-DETAILS

ACS880-01-105A-3+E201

ACS880-01-105A-3+E201 PN: 55KW, IN: 105A



General Information

Global Commercial Alias	ACS880-01-105A-3+E201
Product ID	3ABD00038205-D
ABB Type Designation	ACS880-01-105A-3+E201
Catalog Description	ACS880-01-105A-3+E201 PN: 55KW, IN: 105A

Long Description

The ACS880-01 drives are customized to meet the particular needs of specific industries, such as oil and gas, mining, metals, chemicals, cement, power plants, material handling, pulp and paper, sawmills, marine, water and wastewater, food and beverage, and automotive. They can control a wide range of applications, including cranes, extruders, winches, winders, conveyors, mixers, compressors, centrifuges, test benches, elevators, extruders, pumps, and fans. The ACS880-01 comes in one compact package for easy installation and commissioning. The drive can be installed on the wall as standard and in a cabinet as an option. The drive offering includes enclosure classes up to IP55, making it suitable for most environments and installations. ACS880-01 drives have all the essential features built-in. These features include as standard a choke for harmonic filtering as well as options like a brake chopper, EMC filter and communication protocol adapter, functional safety, external output filters, and I/O extension modules.

Ordering

Country of Origin	China (CN)
Customs Tariff Number	85044099

Invoice Description	ACS880-01-105A-3+E201 PN: 55KW, IN: 105A
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions	
Product Net Weight	45 kg
Product Net Depth / Length	357 mm
Product Net Height	726 mm
Product Net Width	251 mm
Package Level 1 Depth / Length	850 mm
Package Level 1 Height	580 mm
Package Level 1 Width	310 mm
Package Level 1 Units	1 carton

Technical	
Number of Phases	3
Degree of Protection	IP21
Enclosure Type NEMA	Type1
Frequency (f)	47.5 ... 63 Hz
Frame Size	R6
Input Voltage (U_{in})	380 ... 415 V
Mounting Type	Wall-mounted_NO UNIT\$
Output Current, Heavy-Duty Use (I_{HD})	87 A
Output Current, Light-Overload Use (I_{LD})	100 A
Output Current, Normal Use (I_n)	105 A
Output Power, Heavy-Duty Use (P_{HD})	45 kW
Output Power, Light-Overload Use (P_{LD})	55 kW
Output Power, Normal Use (P_n)	55 kW
Efficiency Level	IE2

Additional Information	
Product Name	Frequency Converter
Classifications	
UNSPSC	39122001
Environmental	
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)

Categories	
Drives → Low Voltage AC Drives → Industrial Drives → ACS880 single drives → ACS880-01 - Wall-mounted single drive	

