

AF1350-30-11-70



AF1350-30-11 100-250V 50/60Hz / 100-250V DC Contactor

General Information

Extended Product Type	AF1350-30-11-70
Product ID	1SFL657001R7011
EAN	7320500250143
Catalog Description	AF1350-30-11 100-250V 50/60Hz / 100-250V DC Contactor
Long Description	A 3-phase Contactor suitable for various applications such as Motor starting, Isolation, By-pass and Distribution application up to max 1000 V. Operated with wide control voltage range 100-250 V, AC/DC

Classifications

Object Classification Code	Q
ETIM 4	EC000066 - Magnet contactor, AC-switching
ETIM 5	EC000066 - Magnet contactor, AC-switching
ETIM 6	EC000066 - Power contactor, AC switching
ETIM 7	EC000066 - Power contactor, AC switching
UNSPSC	39121529
IDEA Granular Category Code (IGCC)	4755 >> Contactors
E-Number (Norway)	4115388
E-Number (Sweden)	4115388

Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	555 mm
Package Level 1 Depth / Length	365 mm
Package Level 1 Height	500 mm
Package Level 1 Gross Weight	34 kg
Package Level 1 EAN	7320500250143
Package Level 2 Units	1 piece

Certificates and Declarations (Document Number)

ABS Certificate	15-LD1408622-PDA
BV Certificate	BV_13409-C0BV
CB Certificate	SEMKO_SE-74013
CCC Certificate	CQC_2003010304101933
CCS Certificate	GB14T00030

cUL Certificate	UL_20130904-E73397
Declaration of Conformity - CE	2CMT2019-005796
DNV GL Certificate	TAE00001W1
EAC Certificate	9AKK107046A8618
Environmental Information	1SFC101014D0201
GL Certificate	GL_20263-04HH
Instructions and Manuals	1SFC101002M5501
LOVAG Certificate	SE-202726
LR Certificate	16-20064
PRS Certificate	TE_2092_880423_16
RINA Certificate	ELE060313XG_002
RMRS Certificate	9AKK107045A6978
RoHS Information	2CMT2019-005796
UL Listing Card	UL_E73397

Technical UL/CSA

Maximum Operating Voltage UL/CSA	Main Circuit 600 V
General Use Rating UL/CSA	(600 V AC) 1350 A
Horsepower Rating UL/CSA	(220 ... 240 V AC) Three Phase 400 hp (440 ... 480 V AC) Three Phase 800 hp (550 ... 600 V AC) Three Phase 1000 hp

Environmental

Ambient Air Temperature	Close to Contactor for Storage -40 ... +70 °C Close to Contactor Fitted with Thermal O/L Relay (0.85 ... 1.1 Uc) -25 ... +50 °C Close to Contactor without Thermal O/L Relay (0.85 ... 1.1 Uc) -40 ... +70 °C
Maximum Operating Altitude Permissible	3000 m
RoHS Status	Following EU Directive 2011/65/EU

Technical

Number of Main Contacts NO	3
Number of Main Contacts NC	0
Number of Auxiliary Contacts NO	1
Number of Auxiliary Contacts NC	1
Rated Operational Voltage	Main Circuit 1000 V
Rated Frequency (f)	Main Circuit 50/60 Hz
Conventional Free-air Thermal Current (I_{th})	acc. to IEC 60947-4-1, Open Contactors q = 40 °C 1350 A
Rated Operational Current AC-1 (I_e)	(1000 V) 40 °C 1350 A (1000 V) 55 °C 1150 A (1000 V) 70 °C 1000 A (690 V) 40 °C 1350 A (690 V) 55 °C 1150 A (690 V) 70 °C 1000 A
Rated Operational Current AC-3 (I_e)	(220 / 230 / 240 V) 55 °C 860 A (380 / 400 V) 55 °C 860 A (415 V) 55 °C 860 A (440 V) 55 °C 860 A (500 V) 55 °C 800 A (690 V) 55 °C 800 A
Rated Operational Power AC-3 (P_e)	(1000 V) 560 KWT (220 / 230 / 240 V) 257 KWT

(380 / 400 V) 475 KWT
 (415 V) 500 KWT
 (440 V) 560 KWT
 (500 V) 560 KWT
 (690 V) 800 KWT

Rated Making Capacity AC-3 acc. to IEC 60947-4-1	10 x I _e AC-3
Rated Short-time Withstand Current (I _{cw})	at 40 °C Ambient Temp, in Free Air, from a Cold State 10 s 8000 A at 40 °C Ambient Temp, in Free Air, from a Cold State 15 min 1600 A at 40 °C Ambient Temp, in Free Air, from a Cold State 1 min 4500 A at 40 °C Ambient Temp, in Free Air, from a Cold State 1 s 10000 A at 40 °C Ambient Temp, in Free Air, from a Cold State 30 s 6000 A
Maximum Breaking Capacity	cos phi=0.45 (cos phi=0.35 for I _e > 100 A) at 440 V 10000 A
Maximum Electrical Switching Frequency	AC-1 60 cycles per hour AC-2 / AC-4 60 cycles per hour AC-3 60 cycles per hour
Rated Operational Current DC-1 (I _e)	(220 V) 3 Poles in Series, 40 °C 1350 A (600 V) 3 Poles in Series, 40 °C 1350 A (850 V) 3 Poles in Series, 40 °C 1350 A
Rated Operational Current DC-3 (I _e)	(220 V) 3 Poles in Series, 40 °C 1350 A (600 V) 3 Poles in Series, 40 °C 1350 A (850 V) 3 Poles in Series, 40 °C 1350 A
Rated Operational Current DC-5 (I _e)	(220 V) 3 Poles in Series, 40 °C 1350 A (600 V) 3 Poles in Series, 40 °C 1350 A (850 V) 3 Poles in Series, 40 °C 1350 A
Rated Insulation Voltage (U _i)	acc. to UL/CSA 600 V acc. to IEC 60947-4-1 and VDE 0110 (Gr. C) 1000 V
Rated Impulse Withstand Voltage (U _{imp})	Main Circuit 8 kV
Mechanical Durability	0.5 million
Maximum Mechanical Switching Frequency	300 cycles per hour
Coil Operating Limits	(acc. to IEC 60947-4-1) 0.85 x U _c Min. ... 1.1 x U _c Max. (at θ ≤ 70 °C)
Rated Control Circuit Voltage (U _c)	50 Hz 100 ... 250 V 60 Hz 100 ... 250 V DC Operation 100 ... 250 V
Coil Consumption	Holding at Max. Rated Control Circuit Voltage 50 Hz 48 V·A Holding at Max. Rated Control Circuit Voltage 60 Hz 48 V·A Holding at Max. Rated Control Circuit Voltage DC 20.5 V·A Pull-in at Max. Rated Control Circuit Voltage 50 Hz 2450 V·A Pull-in at Max. Rated Control Circuit Voltage 60 Hz 2450 V·A Pull-in at Max. Rated Control Circuit Voltage DC 2290 V·A
Operate Time	Between Coil De-energization and NC Contact Closing 35 ... 55 ms Between Coil De-energization and NO Contact Opening 35 ... 55 ms Between Coil Energization and NC Contact Opening 50 ... 80 ms Between Coil Energization and NO Contact Closing 50 ... 80 ms
Connecting Capacity Main Circuit	Bar 100 mm
Connecting Capacity Auxiliary Circuit	Flexible with Ferrule 1 x 0.75 ... 2.5 m ² Flexible with Insulated Ferrule 1 x 0.75 ... 2.5 m ² Flexible 2x0.75 ... 2.5 m ² Solid 2 x 1 ... 4 m ² Stranded 1 x 1 ... 4 m ²
Degree of Protection	acc. to IEC 60529, IEC 60947-1, EN 60529 Coil Terminals IP20 acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP00
Terminal Type	Main Circuit: Bars

Dimensions

Product Net Width	438 mm
Product Net Depth / Length	244 mm
Product Net Height	392 mm
Product Net Weight	32 kg

Popular Downloads

Data Sheet, Technical Information	1SBC100192C0206
Instructions and Manuals	1SFC101002M5501
Dimension Diagram	53540930-7

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85364900

Categories

Low Voltage Products and Systems → Control Products → Contactors → Block Contactors

