

PRODUCT-DETAILS

ACS580-01-073A-4

LV AC general purpose wall-mounted drive, IEC: Pn 37 kW, 73 A (ACS580-01-073A-4)



General Information	
Global Commercial Alias	ACS580-01-073A-4
Product ID	3ABD00045434-D
ABB Type Designation	ACS580-01-073A-4
Catalog Description	LV AC general purpose wall-mounted drive, IEC: Pn 37 kW, 73 A (ACS580-01-073A-4)
Long Description	The ACS580-01 is plug-in ready to control your compressors, conveyors, pumps, extruders, centrifuges, mixers, fans, and many other variable and constant torque applications, in a variety of light industries, including food and beverage, plastic, textile, material handling, and agriculture. All essential features are built-in as standard, simplifying drive selection, and making additional hardware unnecessary. A versatile and straightforward settings menu and assistants enable fast setup, commissioning, use, and maintenance, while a rugged and robust design make it a good fit for various environments. With the ACS580 drives, you can easily take full control of your processes to comprehensively manage your plant. The wall-mounted ACS580-01 comes in an IP21 enclosure as standard. In addition, IP55 and flange mounting units are available.

Ordering	
Country of Origin	China (CN)
Customs Tariff Number	85044099
Invoice Description	ACS580-01-073A-4 PN: 37kW, IN: 73A

Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions

Product Net Weight	19 kg
Product Net Depth / Length	258 mm
Product Net Height	600 mm
Product Net Width	203 mm
Package Level 1 Units	0 carton

Technical

Number of Phases	3
Degree of Protection	IP21
Enclosure Type NEMA	Type1
Frequency (f)	47.5 ... 63 Hz
Frame Size	R4
Input Voltage (U_{in})	380 ... 480 V
Mounting Type	Wall-mounted_NO UNIT\$
Output Current, Heavy-Duty Use (I_{HD})	61 A
Output Current, Light-Overload Use (I_{LD})	68.4 A
Output Current, Normal Use (I_n)	73 A
Output Power, Heavy-Duty Use (P_{HD})	30 kW
Output Power, Light-Overload Use (P_{LD})	37 kW
Output Power, Normal Use (P_n)	37 kW
Efficiency Level	IE2
Complete Drive Module Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Relative Loss	Efficiency
0 / 25 %	295 W	0.6 %	90.1 %
0 / 50 %	392 W	0.8 %	93.0 %
0 / 100 %	726 W	1.4 %	93.4 %
50 / 25 %	324 W	0.6 %	94.5 %
50 / 50 %	454 W	0.9 %	96.0 %
50 / 100 %	866 W	1.7 %	96.1 %
90 / 50 %	527 W	1.0 %	97.4 %
90 / 100 %	1120 W	2.2 %	97.2 %

Additional Information

Product Name	Frequency Converter
--------------	---------------------

Classifications

UNSPSC	39122001
--------	----------

Environmental

WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)
---------------	---

Categories

Drives → Low Voltage AC Drives → General Purpose Drives → ACS580-01 - Wall-mounted drive

