

PRODUCT-DETAILS

# ACS530-01-088A-4+J400

## ACS530-01-088A-4+J400 PN: 45kW, IN: 88A



General Information	
Global Commercial Alias	ACS530-01-088A-4+J400
Product ID	3ABD00046341
ABB Type Designation	ACS530-01-088A-4+J400
Catalog Description	ACS530-01-088A-4+J400 PN: 45kW, IN: 88A
Long Description	<p>The ACS530-01 can control your compressors, conveyors, pumps, centrifuges, fans, and many other variable and simple constant torque applications, in a variety of light industries, including food and beverage, plastic, textile, material handling, and agriculture. All essential features are built-in as standard, simplifying drive selection, and making additional hardware unnecessary. The basic control panel enable fast setup, commissioning, use, and maintenance, while a rugged and robust design make it a good fit for various environments.</p> <p>The wall-mounted ACS530-01 comes in an IP20 enclosure as standard.</p>

Ordering	
Country of Origin	China (CN)
Customs Tariff Number	85044099
Invoice Description	ACS530-01-088A-4+J400 PN: 45kW, IN: 88A
Made To Order	No
Minimum Order Quantity	1 piece

Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions

Product Net Weight	26.5 kg
Product Net Depth / Length	295 mm
Product Net Height	596 mm
Product Net Width	203 mm
Package Level 1 Depth / Length	830 mm
Package Level 1 Height	510 mm
Package Level 1 Width	280 mm
Package Level 1 Units	1 carton

Technical

Number of Phases	3
Degree of Protection	IP20
Enclosure Type NEMA	Open Type
Frequency (f)	47.5 ... 63 Hz
Frame Size	R5
Input Voltage ( $U_{in}$ )	380 ... 500 V
Mounting Type	Wall-mounted_NO UNIT\$
Output Current, Light-Overload Use ( $I_{LD}$ )	82.7 A
Output Current, Normal Use ( $I_n$ )	88 A
Output Power, Light-Overload Use ( $P_{LD}$ )	45 kW
Output Power, Normal Use ( $P_n$ )	45 kW
Efficiency Level	IE2
Complete Drive Module Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Relative Loss	Efficiency
0 / 25 %	294 W	0.5 %	91.9 %
0 / 50 %	402 W	0.7 %	94.1 %
0 / 100 %	767 W	1.3 %	94.3 %
50 / 25 %	325 W	0.5 %	95.5 %
50 / 50 %	469 W	0.8 %	96.6 %
50 / 100 %	915 W	1.5 %	96.6 %
90 / 50 %	545 W	0.9 %	97.8 %
90 / 100 %	1139 W	1.9 %	97.6 %

Additional Information

Product NameFrequency Converter

Classifications

UNSPSC39122001

Environmental

WEEE CategoryProduct Not in WEEE Scope

Categories

Drives → Low Voltage AC Drives → General Purpose Drives → ACS530-01 - Wall-mounted drive

