

PRODUCT-DETAILS

ACH580-01-363A-4+0J400

LV AC wall-mounted drive for HVAC, IEC: Pn
200 kW, 363 A (ACH580-01-363A-4+0J400)



General Information

Global Commercial Alias	ACH580-01-363A-4+0J400
Product ID	3ABD00046056-D
ABB Type Designation	ACH580-01-363A-4+0J400
Catalog Description	LV AC wall-mounted drive for HVAC, IEC: Pn 200 kW, 363 A (ACH580-01-363A-4+0J400)
Long Description	<p>The ACH580 HVAC drive offering has all key features built-in to control fans, pumps and compressors, and more complex equipment like air-handling units and chillers, ensuring a smooth, energy-efficient operation of your HVAC systems in normal and mission-critical situations. The built-in features significantly reduce installation time and the intuitive control panel with an HVAC-specific primary settings menu and help assistants make startup, commissioning, and operation easy. The optional Bluetooth® capability enables the commissioning and monitoring of the drive from a distance. The ACH580-01 comes in an IP21 enclosure and can be installed on the wall as standard. In addition, IP55 and flange mounting units are available.</p>

Ordering

Country of Origin	China (CN)
Customs Tariff Number	85044099
Invoice Description	ACH580-01-363A-4+0J400 PN: 200kW, IN: 363A
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece

Quote Only	No
Selling Unit of Measure	piece

Dimensions	
Product Net Weight	98 kg
Product Net Depth / Length	418 mm
Product Net Height	955 mm
Product Net Width	380 mm
Package Level 1 Units	0 carton

Technical	
Number of Phases	3
Degree of Protection	IP21
Enclosure Type NEMA	Type1
Frequency (f)	47.5 ... 63 Hz
Frame Size	R9
Input Voltage (U_{in})	380 ... 500 V
Mounting Type	Wall-mounted_NO UNIT\$
Output Current, Heavy-Duty Use (I_{HD})	293 A
Output Current, Light-Overload Use (I_{LD})	345 A
Output Current, Normal Use (I_n)	363 A
Output Power, Heavy-Duty Use (P_{HD})	160 kW
Output Power, Light-Overload Use (P_{LD})	200 kW
Output Power, Normal Use (P_n)	200 kW
Efficiency Level	IE2
Complete Drive Module Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Relative Loss	Efficiency
0 / 25 %	1231 W	0.5 %	91.6 %
0 / 50 %	1744 W	0.7 %	93.8 %
0 / 100 %	3267 W	1.3 %	94.1 %
50 / 25 %	1334 W	0.5 %	95.4 %
50 / 50 %	1943 W	0.8 %	96.6 %
50 / 100 %	3772 W	1.5 %	96.7 %
90 / 50 %	2275 W	0.9 %	97.8 %
90 / 100 %	4839 W	1.9 %	97.6 %

Additional Information	
Product Name	Frequency Converter
Classifications	
UNSPSC	39122001
Environmental	
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)

Categories
Drives → Low Voltage AC Drives → Industry-Specific Drives → Drives for HVAC → ACH580-01 - Wall-mounted drive for HVAC

