

PRODUCT-DETAILS

ACS530-01-206A-4+X1645

ACS530-01-206A-4+X1645 PN: 110kW, IN: 206A



General Information

Global Commercial Alias	ACS530-01-206A-4+X1645
Product ID	3ABD00046315
ABB Type Designation	ACS530-01-206A-4+X1645
Catalog Description	ACS530-01-206A-4+X1645 PN: 110kW, IN: 206A
Long Description	<p>The ACS530-01 can control your compressors, conveyors, pumps, centrifuges, fans, and many other variable and simple constant torque applications, in a variety of light industries, including food and beverage, plastic, textile, material handling, and agriculture. All essential features are built-in as standard, simplifying drive selection, and making additional hardware unnecessary. The basic control panel enable fast setup, commissioning, use, and maintenance, while a rugged and robust design make it a good fit for various environments. The wall-mounted ACS530-01 comes in an IP20 enclosure as standard.</p>

Ordering

Country of Origin	China (CN)
Customs Tariff Number	85044099
Invoice Description	ACS530-01-206A-4+X1645 PN: 110kW, IN: 206A
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No

Selling Unit of Measure piece

Dimensions	
Product Net Weight	49.6 kg
Product Net Depth / Length	370 mm
Product Net Height	600 mm
Product Net Width	284 mm
Package Level 1 Depth / Length	970 mm
Package Level 1 Height	600 mm
Package Level 1 Width	380 mm
Package Level 1 Units	1 carton

Technical	
Frame Size	R7
Efficiency Level	IE2

Additional Information	
Product Name	Frequency Converter

Classifications	
UNSPSC	39122001

Environmental	
WEEE Category	Product Not in WEEE Scope

Categories	
Drives → Low Voltage AC Drives → General Purpose Drives → ACS530-01 - Wall-mounted drive	

