

PRODUCT-DETAILS

ACQ531-01-017A-4

ACQ531-01-017A-4 PN: 7.5kW, IN: 17A



General Information

Global Commercial Alias	ACQ531-01-017A-4
Product ID	3ABD00046381
ABB Type Designation	ACQ531-01-017A-4
Catalog Description	ACQ531-01-017A-4 PN: 7.5kW, IN: 17A

Long Description

The ACQ531-01 drives deliver innovative pump features for the water and wastewater industry, securing energy efficient flow of water and wastewater in your pumping solutions. This robust and compact wall-mounted drive has built-in simple pump application functionality. Usability is further enhanced with the optional intuitive Hand-Off-Auto control panel, the PC tool Drive composer and an optional Bluetooth® control panel. The built-in energy calculator visualizes the energy savings achieved with the use of the drive. The ACQ531-01 variant comes in an IP20 enclosure as standard and can be installed on the wall.

Ordering

Country of Origin	China (CN)
Customs Tariff Number	85044099
Invoice Description	ACQ531-01-017A-4 PN: 7.5kW, IN: 17A
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No

Selling Unit of Measure

piece

Dimensions	
Product Net Weight	2.5 kg
Product Net Depth / Length	207 mm
Product Net Height	220 mm
Product Net Width	172 mm
Package Level 1 Depth / Length	280 mm
Package Level 1 Height	265 mm
Package Level 1 Width	250 mm
Package Level 1 Units	1 carton

Technical	
Number of Phases	3
Degree of Protection	IP20
Enclosure Type NEMA	Open Type
Frequency (f)	47.5 ... 63 Hz
Frame Size	B2
Input Voltage (U_{in})	380 ... 480 V
Mounting Type	Module_NO UNIT\$
Output Current, Light-Overload Use (I_{LD})	16.2 A
Output Current, Normal Use (I_n)	17 A
Output Power, Light-Overload Use (P_{LD})	7.5 kW
Output Power, Normal Use (P_n)	7.5 kW
Apparent Power Output	12.0 kV·A
Efficiency Level	IE2
Standby Loss	25 W
Complete Drive Module Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Relative Loss	Efficiency
0 / 25 %	91 W	0.8 %	87.3 %
0 / 50 %	114 W	1 %	91.3 %
0 / 100 %	193 W	1.6 %	92.6 %
50 / 25 %	96 W	0.8 %	93.1 %
50 / 50 %	125 W	1.1 %	95.3 %
50 / 100 %	220 W	1.9 %	95.8 %
90 / 50 %	141 W	1.2 %	97 %
90 / 100 %	259 W	2.2 %	97.2 %

Temperature Rating

Maximum 40 °C

Additional Information	
Product Name	Frequency Converter
Classifications	
UNSPSC	39122001
Environmental	
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories
Drives → Low Voltage AC Drives → Industry-Specific Drives → Drives for water → ACQ531-01 - Wall-mounted drive for water and wastewater

