

PRODUCT-DETAILS

ACH531-01-206A-4+J400

LV AC wall-mounted drive for HVAC, IEC: Pn
110 kW, 206 A (ACH531-01-206A-4+J400)



General Information

Global Commercial Alias	ACH531-01-206A-4+J400
Product ID	3ABD00046774
ABB Type Designation	ACH531-01-206A-4+J400
Catalog Description	LV AC wall-mounted drive for HVAC, IEC: Pn 110 kW, 206 A (ACH531-01-206A-4+J400)
Long Description	<p>The ACH531 drive offering has all key features built-in to control fans, pumps and compressors, and more complex equipment like air-handling units and chillers, ensuring a smooth, energy-efficient operation of your HVAC systems in normal and mission-critical situations. The built-in features significantly reduce installation time and the standard basic control panel can make startup, commissioning, and operation easy. The optional Bluetooth® capability enables the commissioning and monitoring of the drive from a distance. The ACH531-01 comes in an IP20 enclosure and can be installed on the wall as standard.</p>

Ordering

Country of Origin	China (CN)
Customs Tariff Number	85044099
Invoice Description	ACH531-01-206A-4+J400 PN: 110kW, IN: 206A
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No

Selling Unit of Measure piece

Dimensions

Product Net Weight	49.6 kg
Product Net Depth / Length	370 mm
Product Net Height	600 mm
Product Net Width	284 mm
Package Level 1 Depth / Length	970 mm
Package Level 1 Height	600 mm
Package Level 1 Width	380 mm
Package Level 1 Units	1 carton

Technical

Number of Phases	3
Degree of Protection	IP20
Enclosure Type NEMA	Open Type
Frequency (f)	47.5 ... 63 Hz
Frame Size	R7
Input Voltage (U_{in})	380 ... 500 V
Mounting Type	Wall-mounted_NO UNIT\$
Output Current, Light-Overload Use (I_{LD})	196 A
Output Current, Normal Use (I_n)	206 A
Output Power, Light-Overload Use (P_{LD})	110 kW
Output Power, Normal Use (P_n)	110 kW
Efficiency Level	IE2
Complete Drive Module Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Relative Loss	Efficiency
0 / 25 %	722 W	0.5 %	91.5 %
0 / 50 %	1001 W	0.7 %	93.7 %
0 / 100 %	1797 W	1.3 %	94.2 %
50 / 25 %	793 W	0.6 %	95.3 %
50 / 50 %	1138 W	0.8 %	96.5 %
50 / 100 %	2116 W	1.5 %	96.7 %
90 / 50 %	1345 W	0.9 %	97.6 %
90 / 100 %	2785 W	2 %	97.5 %

Additional Information

Product Name	frequency converter
--------------	---------------------

Classifications	
UNSPSC	39122001

Environmental	
WEEE Category	Product Not in WEEE Scope

Categories	
Drives → Low Voltage AC Drives → Industry-Specific Drives → Drives for HVAC → ACH531-01 - Wall-mounted drive for HVAC	

