

PRODUCT-DETAILS

ACS880-01-052A-5+E201

ACS880-01-052A-5+E201 PN: 30KW, IN: 52A



General Information

Global Commercial Alias	ACS880-01-052A-5+E201
Product ID	3ABD00047001-D
ABB Type Designation	ACS880-01-052A-5+E201
Catalog Description	ACS880-01-052A-5+E201 PN: 30KW, IN: 52A

Long Description

The ACS880-01 drives are customized to meet the particular needs of specific industries, such as oil and gas, mining, metals, chemicals, cement, power plants, material handling, pulp and paper, sawmills, marine, water and wastewater, food and beverage, and automotive. They can control a wide range of applications, including cranes, extruders, winches, winders, conveyors, mixers, compressors, centrifuges, test benches, elevators, extruders, pumps, and fans. The ACS880-01 comes in one compact package for easy installation and commissioning. The drive can be installed on the wall as standard and in a cabinet as an option. The drive offering includes enclosure classes up to IP55, making it suitable for most environments and installations. ACS880-01 drives have all the essential features built-in. These features include as standard a choke for harmonic filtering as well as options like a brake chopper, EMC filter and communication protocol adapter, functional safety, external output filters, and I/O extension modules.

Ordering

Country of Origin	China (CN)
Customs Tariff Number	85044099
Invoice Description	ACS880-01-052A-5+E201 PN: 30KW, IN: 52A
Made To Order	No

Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Container Information

Gross Volume	31 dm³
--------------	--------

Dimensions

Product Net Weight	18.5 kg
Product Net Depth / Length	274 mm
Product Net Height	576 mm
Product Net Width	203 mm
Package Level 1 Depth / Length	685 mm
Package Level 1 Height	330 mm
Package Level 1 Width	290 mm
Package Level 1 Units	1 carton

Technical

Number of Phases	3
Degree of Protection	IP21
Enclosure Type NEMA	Type1
Frequency (f)	47.5 ... 63 Hz
Frame Size	R4
Input Voltage (U _{in})	380 ... 500 V
Mounting Type	Wall-mounted_NO UNIT\$
Output Current, Heavy-Duty Use (I _{HD})	40 A
Output Current, Light-Overload Use (I _{LD})	49 A
Output Current, Normal Use (I _n)	52 A
Output Power, Heavy-Duty Use (P _{HD})	22 kW
Output Power, Light-Overload Use (P _{LD})	30 kW
Output Power, Normal Use (P _n)	30 kW
Efficiency Level	IE2

Additional Information

Product Name

Frequency Converter

Classifications

UNSPSC

39122001

Environmental

WEEE Category

Product Not in WEEE Scope

Categories

Drives → Low Voltage AC Drives → Industrial Drives → ACS880 single drives → ACS880-01 - Wall-mounted single drive

