

PRODUCT-DETAILS

ACQ580-01-088A-4+X1666+N7560

LV AC wall-mounted drive for water and wastewater (ACQ580-01-088A-4+X1666+N7560)



General Information

Global Commercial Alias	ACQ580-01-088A-4+X1666+N7560
Product ID	3ABD00048739-D
ABB Type Designation	ACQ580-01-088A-4+X1666+N7560
Catalog Description	LV AC wall-mounted drive for water and wastewater (ACQ580-01-088A-4+X1666+N7560)
Long Description	<p>The ACQ580-01 drives deliver innovative pump features for the water and wastewater industry, securing energy efficient flow of water and wastewater in your pumping solutions. This robust and compact wall-mounted drive has built-in pump application functionality such as sensorless flow calculation, multipump control, level control, soft pipe fill, dry run protection, quick ramps, and a solution for keeping the impeller of the pump clean. Usability is further enhanced with the intuitive Hand-Off-Auto control panel, the PC tool Drive composer and an optional Bluetooth® control panel. The built-in energy calculator visualizes the energy savings achieved with the use of the drive. The ACQ580-01 variant comes in an IP21 enclosure as standard and can be installed on the wall. In addition, IP55 and flange mounting units are available.</p>

Ordering

Country of Origin	China (CN)
Customs Tariff Number	85044099
Invoice Description	ACQ580-01-088A-4+X1666+N7560 PN: 45kW, IN: 88A
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions	
Product Net Weight	28.5 kg
Product Net Depth / Length	295 mm
Product Net Height	732 mm
Product Net Width	203 mm
Package Level 1 Units	0 carton

Technical	
Frame Size	R5
Efficiency Level	IE2

Additional Information	
Product Name	Frequency Converter

Classifications	
UNSPSC	39122001

Environmental	
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)

Categories	
Drives → Low Voltage AC Drives → Industry-Specific Drives → Drives for water → ACQ580-01 - Wall-mounted drive for water and wastewater	

