

PRODUCT-DETAILS

ACS580-01-09A5-4+P973

LV AC general purpose wall-mounted drive, IEC:
Pn 4 kW, 9.4 A (ACS580-01-09A5-4+P973)



General Information

Global Commercial Alias	ACS580-01-09A5-4+P973
Product ID	3ABD00048283-D
ABB Type Designation	ACS580-01-09A5-4+P973
Catalog Description	LV AC general purpose wall-mounted drive, IEC: Pn 4 kW, 9.4 A (ACS580-01-09A5-4+P973)
Long Description	<p>The ACS580-01 is plug-in ready to control your compressors, conveyors, pumps, extruders, centrifuges, mixers, fans, and many other variable and constant torque applications, in a variety of light industries, including food and beverage, plastic, textile, material handling, and agriculture. All essential features are built-in as standard, simplifying drive selection, and making additional hardware unnecessary. A versatile and straightforward settings menu and assistants enable fast setup, commissioning, use, and maintenance, while a rugged and robust design make it a good fit for various environments. With the ACS580 drives, you can easily take full control of your processes to comprehensively manage your plant. The wall-mounted ACS580-01 comes in an IP21 enclosure as standard. In addition, IP55 and flange mounting units are available.</p>

Ordering

Country of Origin	China (CN)
Customs Tariff Number	85044099
Invoice Description	ACS580-01-09A5-4+P973 PN: 4kW, IN: 9.4A
Made To Order	No
Minimum Order Quantity	1 piece

Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions

Product Net Weight	4.6 kg
Product Net Depth / Length	223 mm
Product Net Height	303 mm
Product Net Width	125 mm
Package Level 1 Units	0 carton

Technical

Number of Phases	3
Degree of Protection	IP21
Enclosure Type NEMA	Type1
Frequency (f)	47.5 ... 63 Hz
Frame Size	R1
Input Voltage (U_{in})	380 ... 500 V
Mounting Type	Wall-mounted_NO UNIT\$
Output Current, Heavy-Duty Use (I_{HD})	7.2 A
Output Current, Light-Overload Use (I_{LD})	8.9 A
Output Current, Normal Use (I_n)	9.4 A
Output Power, Heavy-Duty Use (P_{HD})	3 kW
Output Power, Light-Overload Use (P_{LD})	4 kW
Output Power, Normal Use (P_n)	4 kW
Efficiency Level	IE2

Complete Drive Module
Efficiency (61800-9-2)

Operating Point Frequency / Current	Absolute Loss	Relative Loss	Efficiency
0 / 25 %	62 W	1.0 %	84.7 %
0 / 50 %	74 W	1.1 %	90.0 %
0 / 100 %	105 W	1.6 %	92.1 %
50 / 25 %	66 W	1.0 %	91.6 %
50 / 50 %	81 W	1.2 %	94.5 %
50 / 100 %	118 W	1.8 %	95.6 %
90 / 50 %	88 W	1.4 %	96.6 %
90 / 100 %	136 W	2.1 %	97.1 %

Additional Information	
Product Name	Frequency Converter
Classifications	
UNSPSC	39122001
Environmental	
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories
Drives → Low Voltage AC Drives → General Purpose Drives → ACS580-01 - Wall-mounted drive

