



PRODUCT-DETAILS

ACS580-01-12A7-4+P974

LV AC general purpose wall-mounted drive, IEC: Pn 5.5 kW, 12.6 A (ACS580-01-12A7-4+P974)



General Information	
Global Commercial Alias	ACS580-01-12A7-4+P974
Product ID	3ABD00048307-D
ABB Type Designation	ACS580-01-12A7-4+P974
Catalog Description	LV AC general purpose wall-mounted drive, IEC: Pn 5.5 kW, 12.6 A (ACS580-01-12A7-4+P974)
Long Description	The ACS580-01 is plug-in ready to control your compressors, conveyors, pumps, extruders, centrifuges, mixers, fans, and many other variable and constant torque applications, in a variety of light industries, including food and beverage, plastic, textile, material handling, and agriculture. All essential features are built-in as standard, simplifying drive selection, and making additional hardware unnecessary. A versatile and straightforward settings menu and assistants enable fast setup, commissioning, use, and maintenance, while a rugged and robust design make it a good fit for various environments. With the ACS580 drives, you can easily take full control of your processes to comprehensively manage your plant. The wall-mounted ACS580-01 comes in an IP21 enclosure as standard. In addition, IP55 and flange mounting units are available.

Ordering	
Country of Origin	China (CN)
Customs Tariff Number	85044099
Invoice Description	ACS580-01-12A7-4+P974 PN: 5.5kW, IN: 12.6A

Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions

Product Net Weight	4.6 kg
Product Net Depth / Length	223 mm
Product Net Height	303 mm
Product Net Width	125 mm
Package Level 1 Units	0 carton

Technical

Number of Phases	3
Degree of Protection	IP21
Enclosure Type NEMA	Type1
Frequency (f)	47.5 ... 63 Hz
Frame Size	R1
Input Voltage (U_{in})	380 ... 500 V
Mounting Type	Wall-mounted_NO UNIT\$
Output Current, Heavy-Duty Use (I_{HD})	9.4 A
Output Current, Light-Overload Use (I_{LD})	12 A
Output Current, Normal Use (I_n)	12.6 A
Output Power, Heavy-Duty Use (P_{HD})	4 kW
Output Power, Light-Overload Use (P_{LD})	5.5 kW
Output Power, Normal Use (P_n)	5.5 kW
Efficiency Level	IE2
Complete Drive Module Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Relative Loss	Efficiency
0 / 25 %	68 W	0.8 %	87.1 %
0 / 50 %	88 W	1.0 %	91.0 %
0 / 100 %	157 W	1.8 %	91.9 %
50 / 25 %	73 W	0.8 %	93.0 %
50 / 50 %	98 W	1.1 %	95.0 %
50 / 100 %	178 W	2.0 %	95.4 %
90 / 50 %	108 W	1.2 %	96.9 %
90 / 100 %	213 W	2.4 %	96.9 %

Additional Information

Product Name	Frequency Converter
--------------	---------------------

Classifications

UNSPSC	39122001
--------	----------

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
---------------	--

Categories

Drives → Low Voltage AC Drives → General Purpose Drives → ACS580-01 - Wall-mounted drive

