



PRODUCT-DETAILS

# ACS580-01-062A-4+J404

## LV AC general purpose wall-mounted drive, IEC: Pn 30 kW, 62 A (ACS580-01-062A-4+J404)



General Information	
Global Commercial Alias	ACS580-01-062A-4+J404
Product ID	3ABD00048860-D
ABB Type Designation	ACS580-01-062A-4+J404
Catalog Description	LV AC general purpose wall-mounted drive, IEC: Pn 30 kW, 62 A (ACS580-01-062A-4+J404)
Long Description	The ACS580-01 is plug-in ready to control your compressors, conveyors, pumps, extruders, centrifuges, mixers, fans, and many other variable and constant torque applications, in a variety of light industries, including food and beverage, plastic, textile, material handling, and agriculture. All essential features are built-in as standard, simplifying drive selection, and making additional hardware unnecessary. A versatile and straightforward settings menu and assistants enable fast setup, commissioning, use, and maintenance, while a rugged and robust design make it a good fit for various environments. With the ACS580 drives, you can easily take full control of your processes to comprehensively manage your plant. The wall-mounted ACS580-01 comes in an IP21 enclosure as standard. In addition, IP55 and flange mounting units are available.

Ordering	
Country of Origin	China (CN)
Customs Tariff Number	85044099
Invoice Description	ACS580-01-062A-4+J404 PN: 30kW, IN: 62A
Made To Order	No
Minimum Order Quantity	1 piece

Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

## Dimensions

Product Net Weight	23.5 kg
Product Net Depth / Length	258 mm
Product Net Height	600 mm
Product Net Width	203 mm
Package Level 1 Units	0 carton

## Technical

Number of Phases	3
Degree of Protection	IP21
Enclosure Type NEMA	Type1
Frequency (f)	47.5 ... 63 Hz
Frame Size	R4
Input Voltage ( $U_{in}$ )	380 ... 500 V
Mounting Type	Wall-mounted_NO UNIT\$
Output Current, Heavy-Duty Use ( $I_{HD}$ )	44.6 A
Output Current, Light-Overload Use ( $I_{LD}$ )	58 A
Output Current, Normal Use ( $I_n$ )	62 A
Output Power, Heavy-Duty Use ( $P_{HD}$ )	22 kW
Output Power, Light-Overload Use ( $P_{LD}$ )	30 kW
Output Power, Normal Use ( $P_n$ )	30 kW
Efficiency Level	IE2

Complete Drive Module  
Efficiency (61800-9-2)

Operating Point Frequency / Current	Absolute Loss	Relative Loss	Efficiency
0 / 25 %	247 W	0.6 %	90.2 %
0 / 50 %	322 W	0.7 %	93.2 %
0 / 100 %	574 W	1.3 %	93.8 %
50 / 25 %	270 W	0.6 %	94.6 %
50 / 50 %	370 W	0.9 %	96.1 %
50 / 100 %	683 W	1.6 %	96.4 %
90 / 50 %	430 W	1.0 %	97.5 %
90 / 100 %	873 W	2.0 %	97.4 %

Additional Information	
Product Name	frequency converter

Classifications	
UNSPSC	39122001

Environmental	
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)

Categories	
Drives → Low Voltage AC Drives → General Purpose Drives → ACS580-01 - Wall-mounted drive	

