

## PRODUCT-DETAILS

# ACS580-01-206A-4+P974

LV AC general purpose wall-mounted drive, IEC:  
Pn 110 kW, 206 A (ACS580-01-206A-4+P974)



## General Information

Global Commercial Alias	ACS580-01-206A-4+P974
Product ID	3ABD00048319-D
ABB Type Designation	ACS580-01-206A-4+P974
Catalog Description	LV AC general purpose wall-mounted drive, IEC: Pn 110 kW, 206 A (ACS580-01-206A-4+P974)

### Long Description

The ACS580-01 is plug-in ready to control your compressors, conveyors, pumps, extruders, centrifuges, mixers, fans, and many other variable and constant torque applications, in a variety of light industries, including food and beverage, plastic, textile, material handling, and agriculture. All essential features are built-in as standard, simplifying drive selection, and making additional hardware unnecessary. A versatile and straightforward settings menu and assistants enable fast setup, commissioning, use, and maintenance, while a rugged and robust design make it a good fit for various environments. With the ACS580 drives, you can easily take full control of your processes to comprehensively manage your plant. The wall-mounted ACS580-01 comes in an IP21 enclosure as standard. In addition, IP55 and flange mounting units are available.

## Ordering

Country of Origin	China (CN)
Customs Tariff Number	85044099
Invoice Description	ACS580-01-206A-4+P974 PN: 110kW, IN: 206A
Made To Order	No
Minimum Order Quantity	1 piece

Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

## Dimensions

Product Net Weight	54 kg
Product Net Depth / Length	370 mm
Product Net Height	880 mm
Product Net Width	284 mm
Package Level 1 Units	0 carton

## Technical

Number of Phases	3
Degree of Protection	IP21
Enclosure Type NEMA	Type1
Frequency (f)	47.5 ... 63 Hz
Frame Size	R7
Input Voltage ( $U_{in}$ )	380 ... 500 V
Mounting Type	Wall-mounted_NO UNIT\$
Output Current, Heavy-Duty Use ( $I_{HD}$ )	169 A
Output Current, Light-Overload Use ( $I_{LD}$ )	196 A
Output Current, Normal Use ( $I_n$ )	206 A
Output Power, Heavy-Duty Use ( $P_{HD}$ )	90 kW
Output Power, Light-Overload Use ( $P_{LD}$ )	110 kW
Output Power, Normal Use ( $P_n$ )	110 kW
Efficiency Level	IE2

Complete Drive Module  
Efficiency (61800-9-2)

Operating Point Frequency / Current	Absolute Loss	Relative Loss	Efficiency
0 / 25 %	722 W	0.5 %	91.5 %
0 / 50 %	1001 W	0.7 %	93.7 %
0 / 100 %	1797 W	1.3 %	94.2 %
50 / 25 %	793 W	0.6 %	95.3 %
50 / 50 %	1138 W	0.8 %	96.5 %
50 / 100 %	2116 W	1.5 %	96.7 %
90 / 50 %	1345 W	0.9 %	97.6 %
90 / 100 %	2785 W	2.0 %	97.5 %

Additional Information	
Product Name	Frequency Converter
Classifications	
UNSPSC	39122001
Environmental	
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)

Categories

Drives → Low Voltage AC Drives → General Purpose Drives → ACS580-01 - Wall-mounted drive

