

PRODUCT-DETAILS

ACS580-01-145A-4+J404

LV AC general purpose wall-mounted drive, IEC: Pn 75 kW, 145 A (ACS580-01-145A-4+J404)



General Information

Global Commercial Alias	ACS580-01-145A-4+J404
Product ID	3ABD00048864-D
ABB Type Designation	ACS580-01-145A-4+J404
Catalog Description	LV AC general purpose wall-mounted drive, IEC: Pn 75 kW, 145 A (ACS580-01-145A-4+J404)

Long Description	The ACS580-01 is plug-in ready to control your compressors, conveyors, pumps, extruders, centrifuges, mixers, fans, and many other variable and constant torque applications, in a variety of light industries, including food and beverage, plastic, textile, material handling, and agriculture. All essential features are built-in as standard, simplifying drive selection, and making additional hardware unnecessary. A versatile and straightforward settings menu and assistants enable fast setup, commissioning, use, and maintenance, while a rugged and robust design make it a good fit for various environments. With the ACS580 drives, you can easily take full control of your processes to comprehensively manage your plant. The wall-mounted ACS580-01 comes in an IP21 enclosure as standard. In addition, IP55 and flange mounting units are available.
------------------	--

Ordering

Country of Origin	China (CN)
Customs Tariff Number	85044099
Invoice Description	ACS580-01-145A-4+J404 PN: 75kW, IN: 145A
Made To Order	No
Minimum Order Quantity	1 piece

Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions

Product Net Weight	45 kg
Product Net Depth / Length	369 mm
Product Net Height	727 mm
Product Net Width	252 mm
Package Level 1 Units	0 carton

Technical

Number of Phases	3
Degree of Protection	IP21
Enclosure Type NEMA	Type1
Frequency (f)	47.5 ... 63 Hz
Frame Size	R6
Input Voltage (U_{in})	380 ... 500 V
Mounting Type	Wall-mounted_NO UNIT\$
Output Current, Heavy-Duty Use (I_{HD})	105 A
Output Current, Light-Overload Use (I_{LD})	138 A
Output Current, Normal Use (I_n)	145 A
Output Power, Heavy-Duty Use (P_{HD})	55 kW
Output Power, Light-Overload Use (P_{LD})	75 kW
Output Power, Normal Use (P_n)	75 kW
Efficiency Level	IE2

Complete Drive Module
Efficiency (61800-9-2)

Operating Point Frequency / Current	Absolute Loss	Relative Loss	Efficiency
0 / 25 %	505 W	0.5 %	91.5 %
0 / 50 %	692 W	0.7 %	93.8 %
0 / 100 %	1238 W	1.2 %	94.4 %
50 / 25 %	557 W	0.6 %	95.3 %
50 / 50 %	791 W	0.8 %	96.5 %
50 / 100 %	1470 W	1.5 %	96.7 %
90 / 50 %	946 W	0.9 %	97.7 %
90 / 100 %	1960 W	2.0 %	97.5 %

Additional Information	
Product Name	frequency converter
Classifications	
UNSPSC	39122001
Environmental	
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)

Categories
Drives → Low Voltage AC Drives → General Purpose Drives → ACS580-01 - Wall-mounted drive

