

## PRODUCT-DETAILS

# ACS580-01-293A-4+J404

LV AC general purpose wall-mounted drive, IEC:  
Pn 160 kW, 293 A (ACS580-01-293A-4+J404)



## General Information

Global Commercial Alias	ACS580-01-293A-4+J404
Product ID	3ABD00048868-D
ABB Type Designation	ACS580-01-293A-4+J404
Catalog Description	LV AC general purpose wall-mounted drive, IEC: Pn 160 kW, 293 A (ACS580-01-293A-4+J404)
Long Description	The ACS580-01 is plug-in ready to control your compressors, conveyors, pumps, extruders, centrifuges, mixers, fans, and many other variable and constant torque applications, in a variety of light industries, including food and beverage, plastic, textile, material handling, and agriculture. All essential features are built-in as standard, simplifying drive selection, and making additional hardware unnecessary. A versatile and straightforward settings menu and assistants enable fast setup, commissioning, use, and maintenance, while a rugged and robust design make it a good fit for various environments. With the ACS580 drives, you can easily take full control of your processes to comprehensively manage your plant. The wall-mounted ACS580-01 comes in an IP21 enclosure as standard. In addition, IP55 and flange mounting units are available.

## Ordering

Country of Origin	China (CN)
Customs Tariff Number	85044099
Invoice Description	ACS580-01-293A-4+J404 PN: 160kW, IN: 293A
Made To Order	No
Minimum Order Quantity	1 piece

Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions	
Product Net Weight	69 kg
Product Net Depth / Length	393 mm
Product Net Height	965 mm
Product Net Width	300 mm
Package Level 1 Units	0 carton

Technical	
Number of Phases	3
Degree of Protection	IP21
Enclosure Type NEMA	Type1
Frequency (f)	47.5 ... 63 Hz
Frame Size	R8
Input Voltage ( $U_{in}$ )	380 ... 500 V
Mounting Type	Wall-mounted_NO UNIT\$
Output Current, Heavy-Duty Use ( $I_{HD}$ )	246 A
Output Current, Light-Overload Use ( $I_{LD}$ )	278 A
Output Current, Normal Use ( $I_n$ )	293 A
Output Power, Heavy-Duty Use ( $P_{HD}$ )	132 kW
Output Power, Light-Overload Use ( $P_{LD}$ )	160 kW
Output Power, Normal Use ( $P_n$ )	160 kW
Efficiency Level	IE2

Complete Drive Module  
Efficiency (61800-9-2)

Operating Point Frequency / Current	Absolute Loss	Relative Loss	Efficiency
0 / 25 %	981 W	0.5 %	91.8 %
0 / 50 %	1382 W	0.7 %	93.9 %
0 / 100 %	2541 W	1.3 %	94.3 %
50 / 25 %	1088 W	0.5 %	95.5 %
50 / 50 %	1582 W	0.8 %	96.5 %
50 / 100 %	3032 W	1.5 %	96.6 %
90 / 50 %	1907 W	0.9 %	97.7 %
90 / 100 %	4071 W	2.0 %	97.5 %

Additional Information	
Product Name	frequency converter
Classifications	
UNSPSC	39122001
Environmental	
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)

Categories
Drives → Low Voltage AC Drives → General Purpose Drives → ACS580-01 - Wall-mounted drive

