

PRODUCT-DETAILS

# ACS530-01-04A0-4+P973

## ACS530-01-04A0-4+P973 PN:1.5kW, IN:4A



General Information	
Global Commercial Alias	ACS530-01-04A0-4+P973
Product ID	3ABD00049989-D
ABB Type Designation	ACS530-01-04A0-4+P973
Catalog Description	ACS530-01-04A0-4+P973 PN:1.5kW, IN:4A
Long Description	<p>The ACS530-01 can control your compressors, conveyors, pumps, centrifuges, fans, and many other variable and simple constant torque applications, in a variety of light industries, including food and beverage, plastic, textile, material handling, and agriculture. All essential features are built-in as standard, simplifying drive selection, and making additional hardware unnecessary. The basic control panel enable fast setup, commissioning, use, and maintenance, while a rugged and robust design make it a good fit for various environments.</p> <p>The wall-mounted ACS530-01 comes in an IP20 enclosure as standard.</p>

Ordering	
Country of Origin	China (CN)
Customs Tariff Number	85044099
Invoice Description	ACS530-01-04A0-4+P973 PN:1.5kW, IN:4A
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No

Selling Unit of Measure

piece

## Dimensions

Product Net Weight	1.6 kg
Product Net Depth / Length	207 mm
Product Net Height	223 mm
Product Net Width	203 mm
Package Level 1 Depth / Length	280 mm
Package Level 1 Height	270 mm
Package Level 1 Width	150 mm
Package Level 1 Units	1 carton

## Technical

Number of Phases	3
Degree of Protection	IP20
Enclosure Type NEMA	Open Type
Frequency (f)	47.5 ... 63 Hz
Frame Size	R0
Input Voltage ( $U_{in}$ )	380 ... 500 V
Mounting Type	Wall-mounted_NO UNIT\$
Output Current, Light-Overload Use ( $I_{LD}$ )	3.8 A
Output Current, Normal Use ( $I_n$ )	4 A
Output Power, Light-Overload Use ( $P_{LD}$ )	1.5 kW
Output Power, Normal Use ( $P_n$ )	1.5 kW
Efficiency Level	IE2
Complete Drive Module Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Relative Loss	Efficiency
0 / 25 %	34 W	1.2 %	81 %
0 / 50 %	39 W	1.4 %	87.9 %
0 / 100 %	50 W	1.8 %	91.4 %
50 / 25 %	36 W	1.3 %	89.5 %
50 / 50 %	41 W	1.5 %	93.5 %
50 / 100 %	55 W	2 %	95.2 %
90 / 50 %	44 W	1.6 %	96 %
90 / 100 %	62 W	2.2 %	96.9 %

## Additional Information

Product Name

Frequency Converter

Classifications	
UNSPSC	39122001

Environmental	
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories	
Drives → Low Voltage AC Drives → General Purpose Drives → ACS530-01 - Wall-mounted drive	

