



PRODUCT-DETAILS

ACS530-01-363A-4+P974

ACS530-01-363A-4+P974 PN:200kW, IN:363A



General Information

Global Commercial Alias	ACS530-01-363A-4+P974
Product ID	3ABD00050031-D
ABB Type Designation	ACS530-01-363A-4+P974
Catalog Description	ACS530-01-363A-4+P974 PN:200kW, IN:363A
Long Description	<p>The ACS530-01 can control your compressors, conveyors, pumps, centrifuges, fans, and many other variable and simple constant torque applications, in a variety of light industries, including food and beverage, plastic, textile, material handling, and agriculture. All essential features are built-in as standard, simplifying drive selection, and making additional hardware unnecessary. The basic control panel enable fast setup, commissioning, use, and maintenance, while a rugged and robust design make it a good fit for various environments.</p> <p>The wall-mounted ACS530-01 comes in an IP20 enclosure as standard.</p>

Ordering

Country of Origin	China (CN)
Customs Tariff Number	85044099
Invoice Description	ACS530-01-363A-4+P974 PN:200kW, IN:363A
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No

Selling Unit of Measure

piece

Dimensions

Product Net Weight	84.8 kg
Product Net Depth / Length	418 mm
Product Net Height	680 mm
Product Net Width	300 mm
Package Level 1 Depth / Length	1160 mm
Package Level 1 Height	650 mm
Package Level 1 Width	490 mm
Package Level 1 Units	1 carton

Technical

Number of Phases	3
Degree of Protection	IP20
Enclosure Type NEMA	Open Type
Frequency (f)	47.5 ... 63 Hz
Frame Size	R9
Input Voltage (U_{in})	380 ... 500 V
Mounting Type	Wall-mounted_NO UNIT\$
Output Current, Light-Overload Use (I_{LD})	345 A
Output Current, Normal Use (I_n)	363 A
Output Power, Light-Overload Use (P_{LD})	200 kW
Output Power, Normal Use (P_n)	200 kW
Efficiency Level	IE2
Complete Drive Module Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Relative Loss	Efficiency
0 / 25 %	1226 W	0.5 %	91.6 %
0 / 50 %	1739 W	0.7 %	93.8 %
0 / 100 %	3262 W	1.3 %	94.2 %
50 / 25 %	1329 W	0.5 %	95.5 %
50 / 50 %	1938 W	0.8 %	96.6 %
50 / 100 %	3767 W	1.5 %	96.7 %
90 / 50 %	2270 W	0.9 %	97.8 %
90 / 100 %	4834 W	1.9 %	97.6 %

Additional Information

Product Name	Frequency Converter
--------------	---------------------

Classifications	
UNSPSC	39122001

Environmental	
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories	
Drives → Low Voltage AC Drives → General Purpose Drives → ACS530-01 - Wall-mounted drive	

