

## PRODUCT-DETAILS

# ACQ531-01-293A-4+0J404

## ACQ531-01-293A-4+0J404 PN: 160kW, IN: 293A



### General Information

Global Commercial Alias	ACQ531-01-293A-4+0J404
Product ID	3ABD00049861
ABB Type Designation	ACQ531-01-293A-4+0J404
Catalog Description	ACQ531-01-293A-4+0J404 PN: 160kW, IN: 293A

#### Long Description

The ACQ531-01 drives deliver innovative pump features for the water and wastewater industry, securing energy efficient flow of water and wastewater in your pumping solutions. This robust and compact wall-mounted drive has built-in simple pump application functionality. Usability is further enhanced with the optional intuitive Hand-Off-Auto control panel, the PC tool Drive composer and an optional Bluetooth® control panel. The built-in energy calculator visualizes the energy savings achieved with the use of the drive. The ACQ531-01 variant comes in an IP20 enclosure as standard and can be installed on the wall.

### Ordering

Country of Origin	China (CN)
Customs Tariff Number	85044099
Invoice Description	ACQ531-01-293A-4+0J404 PN: 160kW, IN: 293A
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No

Selling Unit of Measure piece

Dimensions	
Product Net Weight	62.8 kg
Product Net Depth / Length	393 mm
Product Net Height	680 mm
Product Net Width	300 mm
Package Level 1 Depth / Length	1160 mm
Package Level 1 Height	650 mm
Package Level 1 Width	490 mm
Package Level 1 Units	1 carton

Technical	
Number of Phases	3
Degree of Protection	IP20
Enclosure Type NEMA	Open Type
Frequency (f)	47.5 ... 63 Hz
Frame Size	R8
Input Voltage ( $U_{in}$ )	380 ... 480 V
Mounting Type	Module_NO UNIT\$
Output Current, Light-Overload Use ( $I_{LD}$ )	278 A
Output Current, Normal Use ( $I_n$ )	293 A
Output Power, Light-Overload Use ( $P_{LD}$ )	160 kW
Output Power, Normal Use ( $P_n$ )	160 kW
Efficiency Level	IE2
Complete Drive Module Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Relative Loss	Efficiency
0 / 25 %	977 W	0.5 %	91.9 %
0 / 50 %	1377 W	0.7 %	93.9 %
0 / 100 %	2536 W	1.2 %	94.3 %
50 / 25 %	1083 W	0.5 %	95.5 %
50 / 50 %	1577 W	0.8 %	96.6 %
50 / 100 %	3028 W	1.5 %	96.6 %
90 / 50 %	1902 W	0.9 %	97.7 %
90 / 100 %	4066 W	2 %	97.5 %

Additional Information	
Product Name	Frequency Converter

Classifications	
UNSPSC	39122001

Environmental	
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories
Drives → Low Voltage AC Drives → Industry-Specific Drives → Drives for water → ACQ531-01 - Wall-mounted drive for water and wastewater

