

PRODUCT-DETAILS

ACQ531-01-018A-4+P974

ACQ531-01-018A-4+P974 PN: 7.5kW, IN: 17A



General Information

Global Commercial Alias	ACQ531-01-018A-4+P974
Product ID	3ABD00058649-D
ABB Type Designation	ACQ531-01-018A-4+P974
Catalog Description	ACQ531-01-018A-4+P974 PN: 7.5kW, IN: 17A

Long Description	The ACQ531-01 drives deliver innovative pump features for the water and wastewater industry, securing energy efficient flow of water and wastewater in your pumping solutions.
	This robust and compact wall-mounted drive has built-in simple pump application functionality. Usability is further enhanced with the optional intuitive Hand-Off-Auto control panel, the PC tool Drive composer and an optional Bluetooth® control panel. The built-in energy calculator visualizes the energy savings achieved with the use of the drive. The ACQ531-01 variant comes in an IP20 enclosure as standard and can be installed on the wall.

Ordering

Country of Origin	China (CN)
Customs Tariff Number	85044099
Invoice Description	ACQ531-01-018A-4+P974 PN: 7.5kW, IN: 17A
Made To Order	No
Minimum Order Quantity	1 piece

Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions

Product Net Weight	6 kg
Product Net Depth / Length	229 mm
Product Net Height	432 mm
Product Net Width	125 mm
Package Level 1 Depth / Length	425 mm
Package Level 1 Height	620 mm
Package Level 1 Width	225 mm
Package Level 1 Units	1 carton

Technical

Number of Phases	3
Degree of Protection	IP20
Enclosure Type NEMA	Open Type
Frequency (f)	47.5 ... 63 Hz
Frame Size	R2
Input Voltage (U_{in})	380 ... 480 V
Mounting Type	Module_NO UNIT\$
Output Current, Light-Overload Use (I_{LD})	16.2 A
Output Current, Normal Use (I_n)	17 A
Output Power, Light-Overload Use (P_{LD})	7.5 kW
Output Power, Normal Use (P_n)	7.5 kW
Complete Drive Module Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Relative Loss	Efficiency
0 / 25 %	90 W	0.8 %	87.4 %
0 / 50 %	112 W	1 %	91.5 %
0 / 100 %	188 W	1.6 %	92.8 %
50 / 25 %	95 W	0.8 %	93.2 %
50 / 50 %	122 W	1 %	95.4 %
50 / 100 %	209 W	1.8 %	96 %
90 / 50 %	133 W	1.1 %	97.1 %
90 / 100 %	238 W	2 %	97.4 %

Additional Information

Product Name Frequency Converter

Classifications

UNSPSC 39122001

Categories

Drives → Low Voltage AC Drives → Industry-Specific Drives → Drives for water → ACQ531-01 - Wall-mounted drive for water and wastewater

