

## PRODUCT-DETAILS

# ACQ531-01-062A-4+P974

## ACQ531-01-062A-4+P974 PN: 30kW, IN: 62A



### General Information

Global Commercial Alias	ACQ531-01-062A-4+P974
Product ID	3ABD00058654-D
ABB Type Designation	ACQ531-01-062A-4+P974
Catalog Description	ACQ531-01-062A-4+P974 PN: 30kW, IN: 62A

### Long Description

The ACQ531-01 drives deliver innovative pump features for the water and wastewater industry, securing energy efficient flow of water and wastewater in your pumping solutions. This robust and compact wall-mounted drive has built-in simple pump application functionality. Usability is further enhanced with the optional intuitive Hand-Off-Auto control panel, the PC tool Drive composer and an optional Bluetooth® control panel. The built-in energy calculator visualizes the energy savings achieved with the use of the drive. The ACQ531-01 variant comes in an IP20 enclosure as standard and can be installed on the wall.

### Ordering

Country of Origin	China (CN)
Customs Tariff Number	85044099
Invoice Description	ACQ531-01-062A-4+P974 PN: 30kW, IN: 62A
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No

Selling Unit of Measure

piece

Dimensions

Product Net Weight	18.5 kg
Product Net Depth / Length	257 mm
Product Net Height	636 mm
Product Net Width	203 mm
Package Level 1 Depth / Length	720 mm
Package Level 1 Height	380 mm
Package Level 1 Width	300 mm
Package Level 1 Units	1 carton

Technical

Number of Phases	3
Degree of Protection	IP20
Enclosure Type NEMA	Open Type
Frequency (f)	47.5 ... 63 Hz
Frame Size	R4
Input Voltage ( $U_{in}$ )	380 ... 480 V
Mounting Type	Module_NO UNIT\$
Output Current, Light-Overload Use ( $I_{LD}$ )	58 A
Output Current, Normal Use ( $I_n$ )	62 A
Output Power, Light-Overload Use ( $P_{LD}$ )	30 kW
Output Power, Normal Use ( $P_n$ )	30 kW
Complete Drive Module Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Relative Loss	Efficiency
0 / 25 %	241 W	0.6 %	90.4 %
0 / 50 %	316 W	0.7 %	93.3 %
0 / 100 %	569 W	1.3 %	93.9 %
50 / 25 %	264 W	0.6 %	94.7 %
50 / 50 %	364 W	0.8 %	96.2 %
50 / 100 %	677 W	1.6 %	96.4 %
90 / 50 %	424 W	1 %	97.5 %
90 / 100 %	867 W	2 %	97.4 %

Additional Information

Product Name	Frequency Converter
--------------	---------------------

## Classifications

UNSPSC

39122001

## Categories

Drives → Low Voltage AC Drives → Industry-Specific Drives → Drives for water → ACQ531-01 - Wall-mounted drive for water and wastewater

