

## PRODUCT-DETAILS

# ACH531-01-02A7-4+P974

## , IEC: Pn 0.75 kW, 2.6 A (ACH531-01-02A7-4+P974)



### General Information

Global Commercial Alias	ACH531-01-02A7-4+P974
Product ID	3ABD00058711-D
ABB Type Designation	ACH531-01-02A7-4+P974
Catalog Description	, IEC: Pn 0.75 kW, 2.6 A (ACH531-01-02A7-4+P974)

#### Long Description

The ACH531 drive offering has all key features built-in to control fans, pumps and compressors, and more complex equipment like air-handling units and chillers, ensuring a smooth, energy-efficient operation of your HVAC systems in normal and mission-critical situations. The built-in features significantly reduce installation time and the standard basic control panel can make startup, commissioning, and operation easy. The optional Bluetooth® capability enables the commissioning and monitoring of the drive from a distance. The ACH531-01 comes in an IP20 enclosure and can be installed on the wall as standard.

### Ordering

Country of Origin	China (CN)
Customs Tariff Number	85044099
Invoice Description	ACH531-01-02A7-4+P974 PN: 0.75kW, IN: 2.6A
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No

Selling Unit of Measure piece

Dimensions

Product Net Weight	4 kg
Product Net Depth / Length	223 mm
Product Net Height	331 mm
Product Net Width	125 mm
Package Level 1 Depth / Length	425 mm
Package Level 1 Height	525 mm
Package Level 1 Width	225 mm
Package Level 1 Units	1 carton

Technical

Number of Phases	3
Degree of Protection	IP20
Enclosure Type NEMA	Open Type
Frequency (f)	47.5 ... 63 Hz
Frame Size	R1
Input Voltage ( $U_{in}$ )	380 ... 500 V
Mounting Type	Wall-mounted_NO UNIT\$
Output Current, Light-Overload Use ( $I_{LD}$ )	2.5 A
Output Current, Normal Use ( $I_n$ )	2.6 A
Output Power, Light-Overload Use ( $P_{LD}$ )	0.75 kW
Output Power, Normal Use ( $P_n$ )	0.75 kW
Complete Drive Module Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Relative Loss	Efficiency
0 / 25 %	28 W	1.5 %	77.6 %
0 / 50 %	30 W	1.6 %	86.2 %
0 / 100 %	34 W	1.9 %	90.9 %
50 / 25 %	28 W	1.6 %	87.5 %
50 / 50 %	31 W	1.7 %	92.5 %
50 / 100 %	37 W	2.1 %	95 %
90 / 50 %	33 W	1.8 %	95.4 %
90 / 100 %	42 W	2.3 %	96.8 %

Additional Information

Product Name	frequency converter
--------------	---------------------

Classifications	
UNSPSC	39122001

Categories
Drives → Low Voltage AC Drives → Industry-Specific Drives → Drives for HVAC → ACH531-01 - Wall-mounted drive for HVAC

