

## PRODUCT-DETAILS

# ACH531-01-018A-4+P974

## , IEC: Pn 7.5 kW, 17 A (ACH531-01-018A-4+P974)



### General Information

Global Commercial Alias	ACH531-01-018A-4+P974
Product ID	3ABD00058718-D
ABB Type Designation	ACH531-01-018A-4+P974
Catalog Description	, IEC: Pn 7.5 kW, 17 A (ACH531-01-018A-4+P974)

#### Long Description

The ACH531 drive offering has all key features built-in to control fans, pumps and compressors, and more complex equipment like air-handling units and chillers, ensuring a smooth, energy-efficient operation of your HVAC systems in normal and mission-critical situations. The built-in features significantly reduce installation time and the standard basic control panel can make startup, commissioning, and operation easy. The optional Bluetooth® capability enables the commissioning and monitoring of the drive from a distance. The ACH531-01 comes in an IP20 enclosure and can be installed on the wall as standard.

### Ordering

Country of Origin	China (CN)
Customs Tariff Number	85044099
Invoice Description	ACH531-01-018A-4+P974 PN: 7.5kW, IN: 17A
Made To Order	No
Minimum Order Quantity	1 piece

Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

### Dimensions

Product Net Weight	6 kg
Product Net Depth / Length	229 mm
Product Net Height	432 mm
Product Net Width	125 mm
Package Level 1 Depth / Length	425 mm
Package Level 1 Height	620 mm
Package Level 1 Width	225 mm
Package Level 1 Units	1 carton

### Technical

Number of Phases	3
Degree of Protection	IP20
Enclosure Type NEMA	Open Type
Frequency (f)	47.5 ... 63 Hz
Frame Size	R2
Input Voltage ( $U_{in}$ )	380 ... 500 V
Mounting Type	Wall-mounted_NO UNIT\$
Output Current, Light-Overload Use ( $I_{LD}$ )	16.2 A
Output Current, Normal Use ( $I_n$ )	17 A
Output Power, Light-Overload Use ( $P_{LD}$ )	7.5 kW
Output Power, Normal Use ( $P_n$ )	7.5 kW
Complete Drive Module Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Relative Loss	Efficiency
0 / 25 %	90 W	0.8 %	87.4 %
0 / 50 %	112 W	1 %	91.5 %
0 / 100 %	188 W	1.6 %	92.8 %
50 / 25 %	95 W	0.8 %	93.2 %
50 / 50 %	122 W	1 %	95.4 %
50 / 100 %	209 W	1.8 %	96 %
90 / 50 %	133 W	1.1 %	97.1 %
90 / 100 %	238 W	2 %	97.4 %

Additional Information	
Product Name	frequency converter

Classifications	
UNSPSC	39122001

Categories	
Drives → Low Voltage AC Drives → Industry-Specific Drives → Drives for HVAC → ACH531-01 - Wall-mounted drive for HVAC	

