

## PRODUCT-DETAILS

# 3ABD00059227-D

## ACS530-04-650A-4+P972 PN: 355kW, IN: 650A



### General Information

Global Commercial Alias	3ABD00059227-D
Product ID	3ABD00059227-D
ABB Type Designation	ACS530-04-650A-4+P972
Catalog Description	ACS530-04-650A-4+P972 PN: 355kW, IN: 650A
Long Description	<p>The ACS530-04 has all essential features built-in as standard, simplifying drive selection, and making additional hardware unnecessary. A versatile and straightforward settings menu and assistants enable fast setup, commissioning, use, and maintenance, while a rugged and robust design makes it a good fit for various environments. With the ACS530 drives, you can easily take full control of your processes to comprehensively manage your plant.</p> <p>The ACS530-04 drive module comes in an IP00 enclosure as standard for cabinet installation. In addition, an IP20 enclosure is available.</p>

### Ordering

Country of Origin	China (CN)
Customs Tariff Number	85044099
Invoice Description	ACS530-04-650A-4+P972 PN: 355kW, IN: 650A
Made To Order	No
Minimum Order Quantity	1 piece

Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Container Information

Gross Volume	161 dm³
--------------	---------

Dimensions

Product Net Weight	161 kg
Product Net Depth / Length	529 mm
Product Net Height	1462 mm
Product Net Width	345 mm
Package Level 1 Depth / Length	500 mm
Package Level 1 Height	2050 mm
Package Level 1 Width	645 mm
Package Level 1 Units	1 carton

Technical

Number of Phases	3
Degree of Protection	IP00
Enclosure Type NEMA	Open Type
Frequency (f)	47.5 ... 63 Hz
Frame Size	R10
Input Voltage ( $U_{in}$ )	380 ... 480 V
Mounting Type	Cabinet-built_NO UNIT\$
Output Current, Light-Overload Use ( $I_{LD}$ )	634 A
Output Current, Normal Use ( $I_n$ )	650 A
Output Power, Light-Overload Use ( $P_{LD}$ )	355 kW
Output Power, Normal Use ( $P_n$ )	355 kW
Complete Drive Module Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Relative Loss	Efficiency
0 / 25 %	2034 W	0.5 %	92.2 %
0 / 50 %	2974 W	0.7 %	94.1 %
0 / 100 %	5631 W	1.3 %	94.3 %
50 / 25 %	2206 W	0.5 %	95.8 %
50 / 50 %	3349 W	0.7 %	96.7 %
50 / 100 %	6544 W	1.5 %	96.8 %
90 / 50 %	3874 W	0.9 %	97.9 %
90 / 100 %	8036 W	1.8 %	97.8 %

Additional Information

Product NameFrequency Converter

Classifications

UNSPSC39122001

Categories

Drives → Low Voltage AC Drives → General Purpose Drives → ACS530-04 - Drive module

