



PRODUCT-DETAILS

3ABD00059228-D

ACS530-04-725A-4+P972 PN: 400kW, IN: 725A



General Information	
Global Commercial Alias	3ABD00059228-D
Product ID	3ABD00059228-D
ABB Type Designation	ACS530-04-725A-4+P972
Catalog Description	ACS530-04-725A-4+P972 PN: 400kW, IN: 725A
Long Description	<p>The ACS530-04 has all essential features built-in as standard, simplifying drive selection, and making additional hardware unnecessary. A versatile and straightforward settings menu and assistants enable fast setup, commissioning, use, and maintenance, while a rugged and robust design makes it a good fit for various environments. With the ACS530 drives, you can easily take full control of your processes to comprehensively manage your plant.</p> <p>The ACS530-04 drive module comes in an IP00 enclosure as standard for cabinet installation. In addition, an IP20 enclosure is available.</p>

Ordering	
Country of Origin	China (CN)
Customs Tariff Number	85044099
Invoice Description	ACS530-04-725A-4+P972 PN: 400kW, IN: 725A
Made To Order	No
Minimum Order Quantity	1 piece

Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Container Information

Gross Volume	161 dm³
--------------	---------

Dimensions

Product Net Weight	180 kg
Product Net Depth / Length	529 mm
Product Net Height	1462 mm
Product Net Width	345 mm
Package Level 1 Depth / Length	500 mm
Package Level 1 Height	2050 mm
Package Level 1 Width	645 mm
Package Level 1 Units	0 carton

Technical

Number of Phases	3
Degree of Protection	IP00
Enclosure Type NEMA	Open Type
Frequency (f)	47.5 ... 63 Hz
Frame Size	R11
Input Voltage ( $U_{in}$ )	380 ... 480 V
Mounting Type	Cabinet-built_NO UNIT\$
Output Current, Light-Overload Use ( $I_{LD}$ )	715 A
Output Current, Normal Use ( $I_n$ )	725 A
Output Power, Light-Overload Use ( $P_{LD}$ )	400 kW
Output Power, Normal Use ( $P_n$ )	400 kW
Complete Drive Module Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Relative Loss	Efficiency
0 / 25 %	2115 W	0.4 %	92.7 %
0 / 50 %	3033 W	0.6 %	94.6 %
0 / 100 %	5564 W	1.1 %	95 %
50 / 25 %	2300 W	0.5 %	96 %
50 / 50 %	3431 W	0.7 %	97 %
50 / 100 %	6504 W	1.3 %	97.1 %
90 / 50 %	4015 W	0.8 %	98 %
90 / 100 %	8095 W	1.6 %	98 %

Additional Information

Product NameFrequency Converter

Classifications

UNSPSC39122001

Categories

Drives → Low Voltage AC Drives → General Purpose Drives → ACS530-04 - Drive module

