

## PRODUCT-DETAILS

# ACS580-01-12A7-4

LV AC general purpose wall-mounted drive, IEC:  
Pn 5.5 kW, 12.6 A (ACS580-01-12A7-4)



## General Information

Global Commercial Alias	ACS580-01-12A7-4
Product ID	3ABD50000038953
ABB Type Designation	ACS580-01-12A7-4
Catalog Description	LV AC general purpose wall-mounted drive, IEC: Pn 5.5 kW, 12.6 A (ACS580-01-12A7-4)
Long Description	The ACS580-01 is plug-in ready to control your compressors, conveyors, pumps, extruders, centrifuges, mixers, fans, and many other variable and constant torque applications, in a variety of light industries, including food and beverage, plastic, textile, material handling, and agriculture. All essential features are built-in as standard, simplifying drive selection, and making additional hardware unnecessary. A versatile and straightforward settings menu and assistants enable fast setup, commissioning, use, and maintenance, while a rugged and robust design make it a good fit for various environments. With the ACS580 drives, you can easily take full control of your processes to comprehensively manage your plant. The wall-mounted ACS580-01 comes in an IP21 enclosure as standard. In addition, IP55 and flange mounting units are available.

## Ordering

Country of Origin	China (CN)
Customs Tariff Number	85044099
Invoice Description	ACS580-01-12A7-4 PN: 5.5kW, IN: 12.6A
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece

Quote Only	No
Selling Unit of Measure	piece

Dimensions

Product Net Weight	4.6 kg
Product Net Depth / Length	223 mm
Product Net Height	303 mm
Product Net Width	125 mm
Package Level 1 Units	0 carton

Technical

Number of Phases	3
Degree of Protection	IP21
Enclosure Type NEMA	Type1
Frequency (f)	47.5 ... 63 Hz
Frame Size	R1
Input Voltage ( $U_{in}$ )	380 ... 480 V
Mounting Type	Wall-mounted_NO UNIT\$
Output Current, Heavy-Duty Use ( $I_{HD}$ )	9.4 A
Output Current, Light-Overload Use ( $I_{LD}$ )	12 A
Output Current, Normal Use ( $I_n$ )	12.6 A
Output Power, Heavy-Duty Use ( $P_{HD}$ )	4 kW
Output Power, Light-Overload Use ( $P_{LD}$ )	5.5 kW
Output Power, Normal Use ( $P_n$ )	5.5 kW
Efficiency Level	IE2
Complete Drive Module Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Relative Loss	Efficiency
0 / 25 %	68 W	0.8 %	87.1 %
0 / 50 %	88 W	1.0 %	91.0 %
0 / 100 %	157 W	1.8 %	91.9 %
50 / 25 %	73 W	0.8 %	93.0 %
50 / 50 %	98 W	1.1 %	95.0 %
50 / 100 %	178 W	2.0 %	95.4 %
90 / 50 %	108 W	1.2 %	96.9 %
90 / 100 %	213 W	2.4 %	96.9 %

Additional Information	
Product Name	Frequency Converter
Classifications	
UNSPSC	39122001
Environmental	
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories
Drives → Low Voltage AC Drives → General Purpose Drives → ACS580-01 - Wall-mounted drive

