

PRODUCT-DETAILS

ACS580-01-018A-4+B056

LV AC general purpose wall-mounted drive, IEC:
Pn 7.5 kW, 17 A (ACS580-01-018A-4+B056)



General Information

Global Commercial Alias	ACS580-01-018A-4+B056
Product ID	3ABD50000038976
ABB Type Designation	ACS580-01-018A-4+B056
Catalog Description	LV AC general purpose wall-mounted drive, IEC: Pn 7.5 kW, 17 A (ACS580-01-018A-4+B056)

Long Description

The ACS580-01 is plug-in ready to control your compressors, conveyors, pumps, extruders, centrifuges, mixers, fans, and many other variable and constant torque applications, in a variety of light industries, including food and beverage, plastic, textile, material handling, and agriculture. All essential features are built-in as standard, simplifying drive selection, and making additional hardware unnecessary. A versatile and straightforward settings menu and assistants enable fast setup, commissioning, use, and maintenance, while a rugged and robust design make it a good fit for various environments. With the ACS580 drives, you can easily take full control of your processes to comprehensively manage your plant. The wall-mounted ACS580-01 comes in an IP21 enclosure as standard. In addition, IP55 and flange mounting units are available.

Ordering

Country of Origin	China (CN)
Customs Tariff Number	85044099
Invoice Description	ACS580-01-018A-4+B056 PN: 7.5kW, IN: 17A
Made To Order	No
Minimum Order Quantity	1 piece

Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions

Product Net Weight	7.5 kg
Product Net Depth / Length	227 mm
Product Net Height	394 mm
Product Net Width	125 mm
Package Level 1 Units	0 carton

Technical

Number of Phases	3
Degree of Protection	IP55
Enclosure Type NEMA	Type12
Frequency (f)	47.5 ... 63 Hz
Frame Size	R2
Input Voltage (U_{in})	380 ... 500 V
Mounting Type	Wall-mounted_NO UNIT\$
Output Current, Heavy-Duty Use (I_{HD})	12.6 A
Output Current, Light-Overload Use (I_{LD})	16.2 A
Output Current, Normal Use (I_n)	17 A
Output Power, Heavy-Duty Use (P_{HD})	5.5 kW
Output Power, Light-Overload Use (P_{LD})	7.5 kW
Output Power, Normal Use (P_n)	7.5 kW
Efficiency Level	IE2

Complete Drive Module
Efficiency (61800-9-2)

Operating Point Frequency / Current	Absolute Loss	Relative Loss	Efficiency
0 / 25 %	91 W	0.8 %	87.2 %
0 / 50 %	114 W	1.0 %	91.4 %
0 / 100 %	189 W	1.6 %	92.7 %
50 / 25 %	96 W	0.8 %	93.1 %
50 / 50 %	124 W	1.1 %	95.3 %
50 / 100 %	210 W	1.8 %	96.0 %
90 / 50 %	134 W	1.1 %	97.1 %
90 / 100 %	240 W	2.0 %	97.4 %

Additional Information	
Product Name	Frequency Converter

Classifications	
UNSPSC	39122001

Environmental	
SCIP	f016e531-e6de-4d1f-aec7-2a367861600c Finland (FI)
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories	
Drives → Low Voltage AC Drives → General Purpose Drives → ACS580-01 - Wall-mounted drive	

