



PRODUCT-DETAILS

ACS355-03E-13A3-2

ACS355-03E-13A3-2 Pn 3,0kW, I2n 13,3A IP20.



General Information	
Global Commercial Alias	ACS355-03E-13A3-2
Product ID	3AUA0000058177
ABB Type Designation	ACS355-03E-13A3-2
EAN	6438177223528
Catalog Description	ACS355-03E-13A3-2 Pn 3,0kW, I2n 13,3A IP20.
Long Description	<p>The ACS355 drives are designed to meet the requirements of an extensive range of machinery applications in food and beverage, material handling, lifting, textile, printing, rubber and plastics, and woodworking applications.</p> <p>The drive is user-friendly, yet it provides a wide range of built-in technology such as the safe torque off functionality and sequence programming, reducing the need for additional control electronics. The product offers options and diverse functionality to cater to the needs set for speed and torque control of AC induction and permanent magnet motors.</p>

Ordering	
Country of Origin	China (CN) Finland (FI)
Customs Tariff Number	85044085
Invoice Description	ACS355-03E-13A3-2 Pn 3,0kW, I2n 13,3A IP20.
Made To Order	No

Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions

Product Net Weight	2.4 kg
Product Net Depth / Length	217 mm
Product Net Height	344 mm
Product Net Width	166 mm
Package Level 1 Depth / Length	350 mm
Package Level 1 Height	170 mm
Package Level 1 Width	220 mm
Package Level 1 Units	1 carton

Technical

Number of Phases	3
Degree of Protection	IP20
Enclosure Type NEMA	Open Type
Frequency (f)	50/60 Hz
Frame Size	R2
Input Voltage (U _{in})	200 ... 240 V
Mounting Type	Module for cabinet building
Communication Protocol	MODBUS LON DeviceNet PROFIBUS CAN EtherNet/IP PROFINET IO TCP/IP Other Bus Systems
Number of Hardware Interfaces	Industrial Ethernet 0 PROFINET 0 RS-232 1 RS-422 0 RS-485 1 Serial TTY 0 USB 0 Parallel 0 Other 1
Includes	Without control unit Without optical interface With PC connection
Analog Inputs	2
Analog Outputs	1
Number of Digital	5/1

In/Outputs

Output Current, Normal Use (I_n)	13.3 A
Output Power, Light-Overload Use (P_{LD})	3 kW
Output Power, Normal Use (P_n)	3 kW
Apparent Power Output	5.3 kV·A
Efficiency Level	IE2
Standby Loss	7 W
Complete Drive Module Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Relative Loss	Efficiency
0 / 25 %	56 W	1.1 %	83.2 %
0 / 50 %	68 W	1.3 %	88.9 %
0 / 100 %	97 W	1.8 %	91.2 %
50 / 25 %	60 W	1.1 %	90.7 %
50 / 50 %	75 W	1.4 %	93.7 %
50 / 100 %	113 W	2.1 %	94.9 %
90 / 50 %	87 W	1.6 %	95.9 %
90 / 100 %	139 W	2.6 %	96.4 %

Temperature Rating	Maximum 40 °C
--------------------	---------------

Additional Information

Product Main Type	ACS355
Product Name	Frequency converter

Classifications

ETIM 8	EC001857 - Frequency converter =< 1 kV
ETIM 9	EC001857 - Frequency converter =< 1 kV
UNSPSC	39122001

Environmental

SCIP	619cb020-631d-4c23-9007-dec8f30bc955 Finland (FI)
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Where Used (as part of "kit")		
Identifier	Description	Type
3AUA0000157182		Kit

Categories		
Drives → Low Voltage AC Drives → Machinery Drives → ACS355 - Machinery Drive		

