

PRODUCT-DETAILS

ACH580-01-026A-4

LV AC wall-mounted drive for HVAC, IEC: Pn 11 kW, 25 A (ACH580-01-026A-4)



General Information

Global Commercial Alias	ACH580-01-026A-4
Product ID	3ABD50000038994
ABB Type Designation	ACH580-01-026A-4
Catalog Description	LV AC wall-mounted drive for HVAC, IEC: Pn 11 kW, 25 A (ACH580-01-026A-4)

Long Description	The ACH580 HVAC drive offering has all key features built-in to control fans, pumps and compressors, and more complex equipment like air-handling units and chillers, ensuring a smooth, energy-efficient operation of your HVAC systems in normal and mission-critical situations. The built-in features significantly reduce installation time and the intuitive control panel with an HVAC-specific primary settings menu and help assistants make startup, commissioning, and operation easy. The optional Bluetooth® capability enables the commissioning and monitoring of the drive from a distance. The ACH580-01 comes in an IP21 enclosure and can be installed on the wall as standard. In addition, IP55 and flange mounting units are available.
------------------	---

Ordering

Country of Origin	China (CN)
Customs Tariff Number	85044099
Invoice Description	ACH580-01-026A-4 PN: 11kW, IN: 25A
Made To Order	No

Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions

Product Net Weight	7.5 kg
Product Net Depth / Length	227 mm
Product Net Height	394 mm
Product Net Width	125 mm
Package Level 1 Units	0 carton

Technical

Number of Phases	3
Degree of Protection	IP21
Enclosure Type NEMA	Type1
Frequency (f)	47.5 ... 63 Hz
Frame Size	R2
Input Voltage (U_{in})	380 ... 480 V
Mounting Type	Wall-mounted_NO UNIT\$
Output Current, Heavy-Duty Use (I_{HD})	17 A
Output Current, Light-Overload Use (I_{LD})	23.8 A
Output Current, Normal Use (I_n)	25 A
Output Power, Heavy-Duty Use (P_{HD})	7.5 kW
Output Power, Light-Overload Use (P_{LD})	11 kW
Output Power, Normal Use (P_n)	11 kW
Efficiency Level	IE2
Complete Drive Module Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Relative Loss	Efficiency
0 / 25 %	126 W	0.7 %	87.9 %
0 / 50 %	162 W	0.9 %	91.6 %
0 / 100 %	284 W	1.6 %	92.6 %
50 / 25 %	135 W	0.8 %	93.4 %
50 / 50 %	180 W	1.0 %	95.4 %
50 / 100 %	322 W	1.9 %	95.8 %
90 / 50 %	196 W	1.1 %	97.1 %
90 / 100 %	383 W	2.2 %	97.2 %

Additional Information

Product Name	Frequency Converter
--------------	---------------------

Classifications

UNSPSC	39122001
--------	----------

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
---------------	--

Categories

Drives → Low Voltage AC Drives → Industry-Specific Drives → Drives for HVAC → ACH580-01 - Wall-mounted drive for HVAC

