

# ACS580-01-169A-4



ACS580-01-169A-4 Pn 90 kW I2n 169 A, Protection class IP21, EMC class C2



## General Information

Global Commercial Alias	ACS580-01-169A-4
Product ID	3AUA0000080505
ABB Type Designation	ACS580-01-169A-4
EAN	6438177305613
Catalog Description	ACS580-01-169A-4 Pn 90 kW I2n 169 A, Protection class IP21, EMC class C2

## Ordering

Country of Origin	Finland (FI)
Customs Tariff Number	85044088
EAN	6438177305613
Invoice Description	ACS580-01-169A-4 Pn 90 kW I2n 169 A, Protection class IP21, EMC class C2
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece
Stocked At (Warehouses)	Central Stock Europe Central Stock Asia FIPSEEXPU US Drive Services FIPSEEXPU014 SGRDC002EXPU CNIAB001EXPU SGIND002EXPU AUABB024EXPU SGIND005EXPU

## Dimensions

Product Net Height	880 mm
Product Net Length	370 mm
Product Net Weight	54 kg
Product Net Width	284 mm

## Technical

Frequency (f)	50/60 Hz
	380 ... 480 V

Input Voltage ( $U_{in}$ )

Number of Phases

3

Output Current, Normal Use

169 A

Output Power, Light-Overload Use

90 kW

Output Power, Normal Use

90 kW

---

## Additional Information

Product Main Type

ACS580

Product Name

Frequency converter

---

## Categories

Drives → Low voltage AC drives → General purpose drives → ACS580-01 - Wall-mounted drive

