

PRODUCT-DETAILS

ACH580-01-293A-4

LV AC wall-mounted drive for HVAC, IEC: Pn 160 kW, 293 A, 400 V, UL: Pld 200 Hp, 260 A (ACH580-01-293A-4)



General Information

Global Commercial Alias	ACH580-01-293A-4
Product ID	3AUA0000080533
ABB Type Designation	ACH580-01-293A-4
EAN	6438177305897
Catalog Description	LV AC wall-mounted drive for HVAC, IEC: Pn 160 kW, 293 A, 400 V, UL: Pld 200 Hp, 260 A (ACH580-01-293A-4)
Long Description	ACH580 HVAC drive offering has all key features built-in to control fans, pumps and compressors, and more complex equipment like air-handling units and chillers, ensuring smooth, energy-efficient operation of your HVAC systems in normal and mission-critical situations. The built-in features significantly reduce installation time and the intuitive control panel with an HVAC-specific primary settings menu and help assistants makes startup, commissioning and operation easy. The optional Bluetooth® capability enables the commissioning and monitoring of the drive from a distance. The ACH580-01 comes in IP21 enclosure and can be installed on the wall as standard. Also, IP55 and flange mounting units are available.

Ordering

Country of Origin	Finland (FI)
Customs Tariff Number	85044086
Invoice Description	ACH580-01-293A-4 PN: 160 kW, IN: 293 A
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No

Selling Unit of Measure piece

Container Information

Gross Volume 113.774 dm³

Dimensions

Product Net Weight	69 kg 152.119 lb
Product Net Depth / Length	393.00 mm 15.47 in
Product Net Height	965.00 mm 37.99 in
Product Net Width	300.00 mm 11.81 in
Package Level 1 Depth / Length	1145.00 mm 45.079 in
Package Level 1 Height	630.00 mm 24.803 in
Package Level 1 Width	485.00 mm 19.094 in
Package Level 1 Units	1 carton

Technical

Number of Phases	3
Degree of Protection	IP21
Enclosure Type NEMA	Type1
Altitude	1000 m 95
Sound dB (A)	65 dB(A)
Multiple Battery Information	Lithium Coin, CR2032, 220 mAh, 3 V, 1 pc, 3 g
Frequency (f)	47 ... 63 Hz
Frame Size	R8
Input Voltage (U _{in})	380 ... 480 V
Mounting Type	Wall-mounted
Communication Protocol	BACNET CAN DeviceNet EtherNet/IP LON MODBUS Other Bus Systems PROFIBUS PROFINET IO TCP/IP
Number of Hardware Interfaces	Industrial Ethernet 0 Other 2 Parallel 2 PROFINET 0 RS-232 0 RS-422 0 RS-485 1 Serial TTY 0 USB 1
Includes	PC connection
Analog Inputs	2
Analog Outputs	2
Number of Digital In/Outputs	6/3
Output Current, Heavy-	246 A

Duty Use (I_{HD})	
Output Current, Light-Overload Use (I_{LD})	278 A
Output Current, Normal Use (I_n)	293 A
Output Power, Heavy-Duty Use (P_{HD})	132 kW
Output Power, Light-Overload Use (P_{LD})	160 kW
Output Power, Normal Use (P_n)	160 kW
Apparent Power Output	203 kV·A
Efficiency Level	IE2
Standby Loss	47 W
Complete Drive Module Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Efficiency	Relative Loss
0/25 %	981 W	91.8 %	0.5 %
0/50 %	1382 W	93.9 %	0.7 %
0/100 %	2541 W	94.3 %	1.3 %
50/25 %	1088 W	95.5 %	0.5 %
50/50 %	1582 W	96.5 %	0.8 %
50/100 %	3032 W	96.6 %	1.5 %
90/50 %	1907 W	97.7 %	0.9 %
90/100 %	4071 W	97.5 %	2.0 %

Temperature Rating	Maximum 40 °C Minimum -15 °C
--------------------	---------------------------------

Additional Information

Product Main Type	ACH580-01
Product Name	Frequency converter

Classifications

ETIM 8	EC001857 - Frequency converter =< 1 kV
ETIM 9	EC001857 - Frequency converter =< 1 kV
UNSPSC	39122001

Environmental

SCIP	392bf175-c6df-4719-8b82-cdb09cfcad61 Finland (FI)
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)

Categories

Drives → Low Voltage AC Drives → Industry-Specific Drives → Drives for HVAC → ACH580-01 - Wall-mounted drive for HVAC

