

PRODUCT-DETAILS

ACS880-07-0583A-5

ACS880-07-0583A-5 PN: 400 kW, IN: 583 A



General Information

Global Commercial Alias	ACS880-07-0583A-5
Product ID	3AUA0000138151
ABB Type Designation	ACS880-07-0583A-5
Catalog Description	ACS880-07-0583A-5 PN: 400 kW, IN: 583 A

Ordering

Country of Origin	Finland (FI)
Customs Tariff Number	85044086
Invoice Description	ACS880-07-0583A-5 PN: 400 kW, IN: 583 A
Made To Order	Yes
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions

Product Net Weight	530 kg 1168 lb
--------------------	-------------------

Product Net Depth / Length	698 mm 27.48 in
Product Net Height	2145 mm 84.45 in
Product Net Width	830 mm 32.68 in
Package Level 1 Depth / Length	1100 mm 43.31 in
Package Level 1 Height	2385 mm 93.90 in
Package Level 1 Width	1144 mm 45.04 in

Technical

Number of Phases	3
Degree of Protection	IP22
Enclosure Type NEMA	Type1
Altitude	1000 m 5 ... 95
Power Factor	0.98
Sound dB (A)	72 dB(A)
Multiple Battery Information	Lithium Coin, CR2032, 2pcs, 3V, 220mAh, 6g
Frequency (f)	48 ... 63 Hz
Frame Size	R10
Input Voltage (U_{in})	380 ... 500 V
Communication Protocol	CAN DeviceNet EtherNet/IP MODBUS Other Bus Systems PROFIsafe PROFIBUS PROFINET IO TCP/IP
Number of Hardware Interfaces	Industrial Ethernet 0 Parallel 0 PROFINET 0 RS-232 0 RS-422 0 RS-485 1 Serial TTY 0 USB 1
Includes	Control unit PC connection
Analog Inputs	2
Analog Outputs	2
Number of Digital In/Outputs	7 / 5
Output Current, Heavy-Duty Use (I_{HD})	414 A
Output Current, Light-Overload Use (I_{LD})	573 A
Output Current, Normal Use (I_n)	583 A
Output Power, Heavy-Duty Use (P_{HD})	250 kW

Output Power, Light-Overload Use (P_{LD})	400 kW
Output Power, Normal Use (P_n)	400 kW
Apparent Power Output	505 kV·A
Standby Loss	427 W
Complete Drive Module Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Efficiency	Relative Loss
0/25 %	2064 W	92.9 %	0.4 %
0/50 %	2866 W	94.9 %	0.6 %
0/100 %	4997 W	95.5 %	1.0 %
50/25 %	2221 W	96.2 %	0.4 %
50/50 %	3160 W	97.2 %	0.6 %
50/100 %	5833 W	97.4 %	1.2 %
90/50 %	3652 W	98.2 %	0.7 %
90/100 %	7200 W	98.2 %	1.4 %

Temperature Rating	Maximum 40 °C Minimum 0 °C
Ecodesign Exemption	Energy efficiency data is not provided for this cabinet-built drive. Cabinet-built drives, with already conform modules, are excluded from the scope of the EU ecodesign requirements (Regulation EU/2019/1781, §2.3.e).

Additional Information

Product Main Type	ACS880-07
Product Name	Frequency converter

Classifications

UNSPSC	39122001
--------	----------

Environmental

SCIP	e1aec134-b168-4e21-9c40-ee5e90c4bab4 Finland (FI)
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)

Categories

Drives → Low Voltage AC Drives → Industrial Drives → ACS880 single drives → ACS880-07 - Cabinet-built single drive

