

## PRODUCT-DETAILS

# ACS880-07-1070A-5

## ACS880-07-1070A-5 PN: 710 kW, IN: 1070 A



### General Information

Global Commercial Alias	ACS880-07-1070A-5
Product ID	3AUA0000142694
ABB Type Designation	ACS880-07-1070A-5
Catalog Description	ACS880-07-1070A-5 PN: 710 kW, IN: 1070 A

### Ordering

Country of Origin	Finland (FI)
Customs Tariff Number	85044086
Invoice Description	ACS880-07-1070A-5 PN: 710 kW, IN: 1070 A
Made To Order	Yes
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

### Dimensions

Product Net Weight	1470 kg 3241 lb
Product Net Depth / Length	698 mm 27.48 in

Product Net Height	2145 mm 84.45 in
Product Net Width	1830 mm 72.05 in
Package Level 1 Depth / Length	1100 mm 43.31 in
Package Level 1 Height	2376 mm 93.54 in
Package Level 1 Width	2294 mm 90.32 in

## Technical

Number of Phases	3
Degree of Protection	IP22
Enclosure Type NEMA	Type1
Altitude	1000 m 5 ... 95
Power Factor	0.98
Sound dB (A)	73 dB(A)
Multiple Battery Information	Lithium Coin, BR2032, 2pcs, 3V, 200mAh, 3g
Frequency (f)	48 ... 63 Hz
Frame Size	1xD8T+2xR8i
Input Voltage ( $U_{in}$ )	380 ... 500 V
Mounting Type	Cabinet-built
Communication Protocol	CAN DeviceNet EtherNet/IP MODBUS Other Bus Systems PROFIsafe PROFIBUS PROFINET IO TCP/IP
Number of Hardware Interfaces	Industrial Ethernet 0 Parallel 0 PROFINET 0 RS-232 0 RS-422 0 RS-485 1 Serial TTY 0 USB 1
Includes	Control unit PC connection
Analog Inputs	4
Analog Outputs	4
Number of Digital In/Outputs	14 / 10
Output Current, Heavy- Duty Use ( $I_{HD}$ )	800 A
Output Current, Light- Overload Use ( $I_{LD}$ )	1027 A
Output Current, Normal Use ( $I_n$ )	1070 A
Output Power, Heavy- Duty Use ( $P_{HD}$ )	560 kW
Output Power, Light- Overload Use ( $P_{LD}$ )	710 kW
Output Power, Normal Use ( $P_n$ )	710 kW

Apparent Power Output	927 kV·A
Efficiency Level	IE2
Standby Loss	163 W
Complete Drive Module	
Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Efficiency	Relative Loss
0/25 %	4547 W	91.6 %	0.5 %
0/50 %	6805 W	93.5 %	0.7 %
0/100 %	12837 W	93.8 %	1.4 %
50/25 %	4859 W	95.5 %	0.5 %
50/50 %	7485 W	96.4 %	0.8 %
50/100 %	14899 W	96.4 %	1.6 %
90/50 %	8432 W	97.7 %	0.9 %
90/100 %	17883 W	97.6 %	1.9 %

Temperature Rating	Maximum 40 °C Minimum 0 °C
Ecodesign Exemption	Energy efficiency data according to IEC-61800-9-2 is available from the ecodesign tool ( <a href="https://ecodesign.drivesmotors.abb.com/">https://ecodesign.drivesmotors.abb.com/</a> ).

Additional Information

Product Main Type	ACS880-07
Product Name	Frequency converter

Classifications

UNSPSC	39122001
--------	----------

Environmental

SCIP	F97239A0-8F1B-4B36-A0F6-34D1783CB8EB Finland (FI)
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)

Categories

Drives → Low Voltage AC Drives → Industrial Drives → ACS880 single drives → ACS880-07 - Cabinet-built single drive

