

PRODUCT-DETAILS

ACS355-03E-23A1-4

ACS355-03E-23A1-4 Pn 11kW, I2n 23,1A IP20.



General Information	
Global Commercial Alias	ACS355-03E-23A1-4
Product ID	3AUA0000058192
ABB Type Designation	ACS355-03E-23A1-4
EAN	6438177223672
Catalog Description	ACS355-03E-23A1-4 Pn 11kW, I2n 23,1A IP20.
Long Description	<p>The ACS355 drives are designed to meet the requirements of an extensive range of machinery applications in food and beverage, material handling, lifting, textile, printing, rubber and plastics, and woodworking applications.</p> <p>The drive is user-friendly, yet it provides a wide range of built-in technology such as the safe torque off functionality and sequence programming, reducing the need for additional control electronics. The product offers options and diverse functionality to cater to the needs set for speed and torque control of AC induction and permanent magnet motors.</p>

Ordering	
Country of Origin	China (CN) Finland (FI)
Customs Tariff Number	85044086
Invoice Description	ACS355-03E-23A1-4 Pn 11kW, I2n 23,1A IP20.
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece

Quote Only	No
Selling Unit of Measure	piece

Dimensions	
Product Net Weight	3.6 kg
Product Net Depth / Length	169 mm
Product Net Height	236 mm
Product Net Width	169 mm
Package Level 1 Depth / Length	327 mm
Package Level 1 Height	220 mm
Package Level 1 Width	200 mm
Package Level 1 Units	1 carton

Technical	
Number of Phases	3
Degree of Protection	IP20
Enclosure Type NEMA	Open Type
Frequency (f)	50/60 Hz
Frame Size	R3
Input Voltage (U _{in})	380 ... 480 V
Mounting Type	Module for cabinet building
Communication Protocol	MODBUS LON DeviceNet PROFIBUS CAN EtherNet/IP PROFINET IO TCP/IP Other Bus Systems
Number of Hardware Interfaces	Industrial Ethernet 0 PROFINET 0 RS-232 1 RS-422 0 RS-485 1 Serial TTY 0 USB 0 Parallel 0 Other 1
Includes	Without control unit Without optical interface With PC connection
Analog Inputs	2
Analog Outputs	1
Number of Digital In/Outputs	5/1
Output Current, Normal Use (I _n)	23.1 A
Output Power, Light-Overload Use (P _{LD})	11 kW
Output Power, Normal Use (P _n)	11 kW

Apparent Power Output	16 kV·A
Efficiency Level	IE2
Standby Loss	10 W

Complete Drive Module
Efficiency (61800-9-2)

Operating Point Frequency / Current	Absolute Loss	Relative Loss	Efficiency
0 / 25 %	108 W	0.7 %	88.7 %
0 / 50 %	140 W	0.9 %	92.1 %
0 / 100 %	248 W	1.5 %	92.9 %
50 / 25 %	118 W	0.7 %	93.7 %
50 / 50 %	162 W	1.0 %	95.5 %
50 / 100 %	293 W	1.8 %	95.9 %
90 / 50 %	185 W	1.2 %	97.1 %
90 / 100 %	365 W	2.3 %	97.1 %

Temperature Rating	Maximum 40 °C
--------------------	---------------

Additional Information

Product Main Type	ACS355
Product Name	Frequency converter

Classifications

ETIM 8	EC001857 - Frequency converter =< 1 kV
ETIM 9	EC001857 - Frequency converter =< 1 kV
UNSPSC	39122001

Environmental

SCIP	43820909-4262-4b16-bb51-6a918585e7ca Finland (FI)
Simplified SCIP	8f75f3b6-5e1c-45d5-aa56-9ff58cc190c5 Belgium (BE) 4583c049-fadc-4cb0-b596-e48858506b9b Netherlands (NL) 281e01b8-fcf4-4fc8-8a1e-68f014c46c51 Denmark (DK) 0c60996c-2ac0-48bf-96c7-a2a1d6c6895a Spain (ES) dd1618c2-b1d7-4409-8e05-e3abc895cbf4 Portugal (PT) abebee28-196c-4d72-8160-fa56590b45ee Estonia (EE)
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Where Used (as part of "kit")

Identifier	Description	Type
3AUA0000157196		Kit

Categories

Drives → Low Voltage AC Drives → Machinery Drives → ACS355 - Machinery Drive

