

PRODUCT-DETAILS

ACS880-07-0470A-7

ACS880-07-0470A-7 PN: 450 kW, IN: 470 A



General Information

Global Commercial Alias	ACS880-07-0470A-7
Product ID	3AUA0000154956
ABB Type Designation	ACS880-07-0470A-7
Catalog Description	ACS880-07-0470A-7 PN: 450 kW, IN: 470 A

Ordering

Country of Origin	Finland (FI)
Customs Tariff Number	85044086
Invoice Description	ACS880-07-0470A-7 PN: 450 kW, IN: 470 A
Made To Order	Yes
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions

Product Net Weight	580 kg 1279 lb
--------------------	-------------------

Product Net Depth / Length	698 mm 27.48 in
Product Net Height	2145 mm 84.45 in
Product Net Width	830 mm 32.68 in
Package Level 1 Depth / Length	1100 mm 43.31 in
Package Level 1 Height	2385 mm 93.90 in
Package Level 1 Width	1144 mm 45.04 in

Technical

Number of Phases	3
Degree of Protection	IP22
Enclosure Type NEMA	Type1
Altitude	1000 m
	5 ... 95
Power Factor	0.98
Sound dB (A)	72 dB(A)
Multiple Battery Information	Lithium Coin, CR2032, 2pcs, 3V, 220mAh, 6g
Frequency (f)	48 ... 63 Hz
Frame Size	R11
Input Voltage (U _{in})	525 ... 690 V
Mounting Type	Cabinet-built
Communication Protocol	CAN DeviceNet EtherNet/IP MODBUS Other Bus Systems PROFIsafe PROFIBUS PROFINET IO TCP/IP
Number of Hardware Interfaces	Industrial Ethernet 0 Parallel 0 PROFINET 0 RS-232 0 RS-422 0 RS-485 1 Serial TTY 0 USB 1
Includes	Control unit PC connection
Analog Inputs	2
Analog Outputs	2
Number of Digital In/Outputs	7 / 5
Output Current, Heavy-Duty Use (I _{HD})	415 A
Output Current, Light-Overload Use (I _{LD})	455 A
Output Current, Normal Use (I _n)	470 A
Output Power, Heavy-	400 kW

Duty Use (P_{HD})	
Output Power, Light-	450 kW
Overload Use (P_{LD})	
Output Power, Normal	450 kW
Use (P_n)	
Apparent Power Output	562 kV-A
Standby Loss	438 W
Complete Drive Module	
Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Efficiency	Relative Loss
0/25 %	2269 W	93.0 %	0.4 %
0/50 %	3061 W	95.1 %	0.5 %
0/100 %	4805 W	96.1 %	0.9 %
50/25 %	2446 W	96.2 %	0.4 %
50/50 %	3388 W	97.3 %	0.6 %
50/100 %	5576 W	97.8 %	1.0 %
90/50 %	3863 W	98.3 %	0.7 %
90/100 %	6531 W	98.5 %	1.2 %

Temperature Rating	Maximum 40 °C Minimum 0 °C
Ecodesign Exemption	Energy efficiency data is not provided for this cabinet-built drive. Cabinet-built drives, with already conform modules, are excluded from the scope of the EU ecodesign requirements (Regulation EU/2019/1781, §2.3.e).

Additional Information

Product Main Type	ACS880-07
Product Name	Frequency converter

Classifications

UNSPSC	39122001
--------	----------

Environmental

SCIP	e1aec134-b168-4e21-9c40-ee5e90c4bab4 Finland (FI)
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)

Categories

Drives → Low Voltage AC Drives → Industrial Drives → ACS880 single drives → ACS880-07 - Cabinet-built single drive

