



PRODUCT-DETAILS

# ACS580-01-293A-4

LV AC general purpose wall-mounted drive,  
IEC: Pn 160 kW, 293 A, 400 V, 480 V (ACS580-01-293A-4)



General Information	
Global Commercial Alias	ACS580-01-293A-4
Product ID	3AUA0000080508
ABB Type Designation	ACS580-01-293A-4
EAN	6438177305644
Catalog Description	LV AC general purpose wall-mounted drive, IEC: Pn 160 kW, 293 A, 400 V, 480 V (ACS580-01-293A-4)
Long Description	<p>The ACS580-01 is plug-in ready to control your compressors, conveyors, pumps, extruders, centrifuges, mixers, fans and many other variable and constant torque applications, in a variety of light industries, including food and beverage, plastic, textile, material handling, and agriculture.</p> <p>All essential features are built-in as standard, simplifying drive selection, and making additional hardware unnecessary. Versatile and straightforward settings menu and assistants enable fast setup, commissioning, use and maintenance, while rugged and robust design makes it a good fit for various environments. With the ACS580 drives you can easily take full control of your processes to comprehensively manage your plant. The wall-mounted ACS580-01 comes in IP21 enclosure as standard. Also, IP55 and flange mounting units are available.</p>

Ordering	
Country of Origin	Finland (FI)
Customs Tariff Number	85044086
Invoice Description	ACS580-01-293A-4 PN: 160 kW, IN: 293 A

Made To Order	Yes
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Container Information

Gross Volume	113.774 dm³
--------------	-------------

Dimensions

Product Net Weight	69 kg 152.119 lb
Product Net Depth / Length	393.00 mm 15.47 in
Product Net Height	965.00 mm 37.99 in
Product Net Width	300.00 mm 11.81 in
Package Level 1 Depth / Length	1145.00 mm 45.079 in
Package Level 1 Height	630.00 mm 24.803 in
Package Level 1 Width	485.00 mm 19.094 in
Package Level 1 Units	1 carton

Technical

Number of Phases	3
Degree of Protection	IP21
Enclosure Type NEMA	Type1
Altitude	1000 m 95
Sound dB (A)	65 dB(A)
Multiple Battery Information	Lithium Coin, CR2032, 220 mAh, 3 V, 1 pc, 3 g
Frequency (f)	47.5 ... 63 Hz
Frame Size	R8
Input Voltage (U <sub>in</sub> )	380 ... 480 V
Mounting Type	Wall-mounted
Communication Protocol	CAN DeviceNet EtherNet/IP MODBUS Other Bus Systems PROFIBUS PROFINET IO TCP/IP
Number of Hardware Interfaces	Industrial Ethernet 0 Other 2 Parallel 2 PROFINET 0 RS-232 0 RS-422 0 RS-485 1

	Serial TTY 0 USB 1
Includes	Control unit PC connection
Analog Inputs	2
Analog Outputs	2
Number of Digital In/Outputs	6 / 3
Output Current, Heavy- Duty Use ( $I_{HD}$ )	246 A
Output Current, Light- Overload Use ( $I_{LD}$ )	278 A
Output Current, Normal Use ( $I_n$ )	293 A
Output Power, Heavy- Duty Use ( $P_{HD}$ )	132 kW
Output Power, Light- Overload Use ( $P_{LD}$ )	160 kW
Output Power, Normal Use ( $P_n$ )	160 kW
Apparent Power Output	203 kV·A
Efficiency Level	IE2
Standby Loss	47 W
Complete Drive Module Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Efficiency	Relative Loss
0/25 %	981 W	91.8 %	0.5 %
0/50 %	1382 W	93.9 %	0.7 %
0/100 %	2541 W	94.3 %	1.3 %
50/25 %	1088 W	95.5 %	0.5 %
50/50 %	1582 W	96.5 %	0.8 %
50/100 %	3032 W	96.6 %	1.5 %
90/50 %	1907 W	97.7 %	0.9 %
90/100 %	4071 W	97.5 %	2.0 %

Temperature Rating	Maximum 40 °C Minimum -15 °C
--------------------	---------------------------------

Additional Information

Product Main Type	ACS580-01
Product Name	Frequency converter

Classifications

ETIM 8	EC001857 - Frequency converter =< 1 kV
ETIM 9	EC001857 - Frequency converter =< 1 kV
UNSPSC	39122001

Environmental

SCIP	392bf175-c6df-4719-8b82-cdb09cfcad61 Finland (FI)
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)

Categories

Drives → Low Voltage AC Drives → General Purpose Drives → ACS580-01 - Wall-mounted drive

