

## PRODUCT-DETAILS

# ACH580-01-206A-4+B056

LV AC wall-mounted drive for HVAC, IEC: Pn 110 kW, 206 A, 400 V, UL: Pld 150 Hp, 180 A (ACH580-01-206A-4+B056)



### General Information

Global Commercial Alias	ACH580-01-206A-4+B056
Product ID	3AUA0000083606
ABB Type Designation	ACH580-01-206A-4+B056
EAN	6438177306375
Catalog Description	LV AC wall-mounted drive for HVAC, IEC: Pn 110 kW, 206 A, 400 V, UL: Pld 150 Hp, 180 A (ACH580-01-206A-4+B056)
Long Description	ACH580 HVAC drive offering has all key features built-in to control fans, pumps and compressors, and more complex equipment like air-handling units and chillers, ensuring smooth, energy-efficient operation of your HVAC systems in normal and mission-critical situations. The built-in features significantly reduce installation time and the intuitive control panel with an HVAC-specific primary settings menu and help assistants makes startup, commissioning and operation easy. The optional Bluetooth® capability enables the commissioning and monitoring of the drive from a distance. The ACH580-01 comes in IP21 enclosure and can be installed on the wall as standard. Also, IP55 and flange mounting units are available.

### Ordering

Country of Origin	Finland (FI)
Customs Tariff Number	85044086
Invoice Description	ACH580-01-206A-4+B056 PN: 110 kW, IN: 206 A
Made To Order	Yes
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No

Selling Unit of Measure piece

Container Information

Gross Volume 95.22 dm³

Dimensions

Product Net Weight	56 kg 123.459 lb
Product Net Depth / Length	381.00 mm 15.000 in
Product Net Height	880.00 mm 34.646 in
Product Net Width	284.00 mm 11.181 in
Package Level 1 Depth / Length	992.00 mm 39.055 in
Package Level 1 Height	568.00 mm 22.362 in
Package Level 1 Width	400.00 mm 15.748 in
Package Level 1 Units	1 carton

Technical

Number of Phases	3
Degree of Protection	IP55
Enclosure Type NEMA	Type12
	95
Multiple Battery Information	Lithium Coin, CR2032, 220 mAh, 3 V, 1 pc, 3 g
Frequency (f)	47.5 ... 63 Hz
Frame Size	R7
Input Voltage (U <sub>in</sub> )	380 ... 480 V
Communication Protocol	BACNET CAN DeviceNet EtherNet/IP LON MODBUS Other Bus Systems PROFIBUS PROFINET IO TCP/IP
Number of Hardware Interfaces	Industrial Ethernet 0 Other 2 Parallel 2 PROFINET 0 RS-232 0 RS-422 0 RS-485 1 Serial TTY 0 USB 1
Includes	With control unit Without optical interface With PC connection
Analog Inputs	2
Analog Outputs	2
Number of Digital In/Outputs	6/3
Output Current, Heavy-Duty Use (I <sub>HD</sub> )	169 A

Output Current, Light-Overload Use ( $I_{LD}$ )	196 A
Output Current, Normal Use ( $I_n$ )	206 A
Output Power, Heavy-Duty Use ( $P_{HD}$ )	90 kW
Output Power, Light-Overload Use ( $P_{LD}$ )	110 kW
Output Power, Normal Use ( $P_n$ )	110 kW
Apparent Power Output	143 kV·A
Efficiency Level	IE2
Standby Loss	36 W
Complete Drive Module Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Efficiency	Relative Loss
0/25 %	722 W	91.5 %	0.5 %
0/50 %	1001 W	93.7 %	0.7 %
0/100 %	1797 W	94.2 %	1.3 %
50/25 %	793 W	95.3 %	0.6 %
50/50 %	1138 W	96.5 %	0.8 %
50/100 %	2116 W	96.7 %	1.5 %
90/50 %	1345 W	97.6 %	0.9 %
90/100 %	2785 W	97.5 %	2.0 %

Temperature Rating	Maximum 40 °C Minimum -15 °C
--------------------	---------------------------------

Additional Information

Product Main Type	ACH580-01
Product Name	Frequency converter

Classifications

ETIM 8	EC001857 - Frequency converter =< 1 kV
ETIM 9	EC001857 - Frequency converter =< 1 kV
UNSPSC	39122001

Environmental

SCIP	93c4256e-49ac-4f3a-a0ee-89382f71d90e Finland (FI)
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)

---

## Categories

---

Drives → Low Voltage AC Drives → Industry-Specific Drives → Drives for HVAC → ACH580-01 - Wall-mounted drive for HVAC

